




Part number and Nominal Voltage injected or stamped.  
Date code stamped.



CIRCUIT DIAGRAM



Dustproof;  
Protection class IP 54 to IEC 529 (EN 60 529);  
Terminals shape similar to 8092-1:  
Coil 6.3 x 0.8 mm  
Load 9.5 x 1.2 mm

PART	MATERIAL	COLOUR
Cover	PA 66 GF 25	Black sim. to RAL 90005
Base	PA 66 GF 25	Black sim. to RAL 90005
Coil Terminals 85 and 86	Cu Sn	Pre-tinned Sn
Load Terminals 30 and 87	E-Cu	Pre-tinned Sn

TE P/N	REV	Part Number	COUNTRY OF ORIGIN
7-1393303-3		V23134-J0052-D642	PORTUGAL
7-1904094-7			CHINA

PROPRIETARY  
THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.

CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD

PAPER SIZE  
A2

APPLICABLE SPEC.:  
ISO 2768 m

FINISH  
DIMENSIONS APPLY PLATING

SCALE 2:1

MATERIAL

TOLERANCE UNLESS SPECIFIED OTHERWISE  
ISO 2768 m

DIMENSIONS IN MM

DATE NAME  
16APR2012 L.Sandoval

DWN. APP. REV. LOCATION PE EVORA

PART NAME  
POWER F RELAY  
NO 70A 12V

STE connectivity

PART NO.  
V23134-J0052-D642-CD

SHT. 1 OF 1

REV. CHANGE ORDER DATE APP. CLASS 3 CUSTOMER DRAWING