



Circuit Diagram



Dustproof;
 Protection class IP 54 to IEC 529 (EN 60 529)
 Terminals shape similar to DIN EN ISO 8092-1
 Coil 6.3 x 0.8 mm
 Load 9.5 x 1.2 mm

PART	MATERIAL	COLOUR
Cover	PA 66 GF 25	Black sim. to RAL 9005
Base	PA 66 GF 25	Black sim. to RAL 9005
Coil Terminals 1 and 2	E-Cu	Pre-tinned Sn
Load terminals 3, 5 and 7	E-Cu	Pre-tinned Sn

TE P/N	Rev.	PART NAME
4-1904060-6	C	V23136-L0031-D642-EV-CBOX

PROPRIETARY <small>THE REPRODUCTION, TRANSMISSION OR USE OF THIS DOCUMENT OR IT'S CONTENTS IS NOT PERMITTED WITHOUT EXPRESSED WRITTEN AUTHORITY. OFFENDERS WILL BE LIABLE FOR ALL DAMAGES. ALL RIGHTS, INCLUDING RIGHTS CREATED BY REGISTERED PATENT(S) GRANTED FOR A UTILITY MODEL OR DESIGN, ARE RESERVED.</small>		CHANGES TO THIS DRAWING MUST BE DONE ONLY IN CAD	PAPER SIZE A2
APPLICABLE SPEC.:		FINISH DIMENSIONS APPLY PLATING	
TOLERANCE UNLESS SPECIFIED OTHERWISE DIMENSIONS IN MM		SCALE 1:1; 2:1	WEIGHT
DWN. 15JAN2014 L.Sandoval APP. REV.		PART NAME Power F-A Latching NO 70A	
CI ECO-17-012619 C --- B --- A ---	DATE 21AUG2017 09JUN017 08MAI2014 15JAN2014	LOCATION PE Evora 	DWG NO. C - V23136-L0031-D642
REV. CHANGE ORDER DATE APP.	CLASS 3	CUSTOMER DRAWING	SHT. 1 OF 1