




CUSTOMER DATA

DRAWN S.ESTES	APPROVAL B.TOEPFER	DATE 10-28-88 03-02-99	SCALE 1=1
TOLERANCE UNLESS SPECIFIED OTHERWISE	0.X = 0.XX = 0.XXX = ANGLES =	+/- .1 +/- .01 +/- .010 +/- 1'	[.254] [.254] [0.25]

CUSTOMER TYCO STANDARD

DO NOT SCALE THIS DRAWING

CHANGES			
REV.	DATE	CO	APP.
	03-02-99	REDRAWN	S.E. B.T.
			

ELECTRICAL CHARACTERISTICS: (ALL DATA APPLIES @ 23°C UNLESS OTHERWISE SPECIFIED)

COIL DATA:

NOMINAL VOLTAGE:	12 VDC
OPERATE VOLTAGE:	7.2 VDC MAXIMUM
RELEASE VOLTAGE:	1.2 VDC MINIMUM
EQUIVALENT COIL RESISTANCE:	79.5 OHMS +/- 10%
OPERATE TIME:	8 mSEC. MAXIMUM EXCLUDING BOUNCE
RELEASE TIME:	8 mSEC. MAXIMUM EXCLUDING BOUNCE
TEMPERATURE RANGE:	STORAGE -40°C TO +155°C OPERATING -40°C TO +85°C OPERATING -40°C TO +125°C (APPLICATION DEPENDENT)

CONTACT DATA: (Contact Data is Formatted N.O./N.C.)

CONTACT ARRANGEMENT:	1 FORM C (SPDT)
CONTACT MATERIAL:	AgNi 0.15 (FINE GRAIN SILVER)
CONTACT MILLIVOLT DROP	200 mV @ 40A ON N.O. CONTACTS (AFTER SWITCHING) 250 mV @ 30A ON N.C. CONTACTS (AFTER SWITCHING)
MAXIMUM MAKE CURRENT:	120A/45A (LAMP) @ 16 VDC
MAXIMUM BREAK CURRENT:	60A/40A @ 16 VDC RESISTIVE
MAXIMUM CONTINUOUS CURRENT	60A/40A @ 23°C, 40A/30A @ 85°C
INITIAL BREAKDOWN CURRENT	500V RMS CONTACTS TO COIL
EXPECTED LIFE:	100,000 OPERATIONS, 40 A, 14 VDC RESISTIVE ON NORMALLY OPEN CONTACT


MECHANICAL CHARACTERISTICS:

EXPECTED LIFE:	10 MILLION OPERATIONS, NO CONTACT LOAD, 20 OPERATIONS PER SECOND MAXIMUM
ENCLOSURE:	EPOXY-SEALED

DRAWN S.ESTES	APPROVAL B.TOEPPER	DATE 10-28-88 03-02-99	SCALE 1=1
------------------	-----------------------	---------------------------	--------------

CUSTOMER TYCO STANDARD




TOLERANCE	0.X	=	+/- .1	[2.54]
UNLESS SPECIFIED	0.XX	=	+/- .01	[.254]
OTHERWISE	0.XXX	=	+/- .010	[0.25]
	ANGLES	=	+/- 1°	



DO NOT SCALE THIS DRAWING

X.XXX = INCHES
[XX.XX] = MILLIMETERS

MARKING TO INCLUDE:
MANUFACTURER'S NAME, MANUFACTURER'S PART NUMBER,
COIL VOLTAGE, CONTACT RATING, SCHEMATIC, COUNTRY OF
ORIGIN, AND DATE CODE



* TERMINAL LOCATIONS APPLY AT THE BASE OF THE TERMINALS