


P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	14APR2023	BDA	MB
AI		DRAWING CLARIFICATION	24AUG2023	BDA	VN

## VERSAFIT V4 TUBING POLYOLEFIN, FLEXIBLE, HEAT-SHRINKABLE, FLAME-RETARDANT



PRODUCT DIMENSIONS  
V4 TUBING DIMENSIONS METRIC

SIZE	AS SUPPLIED				AS RECOVERED			
	INSIDE DIAMETER "D"		WALL THICKNESS NOMINAL "W1"		INSIDE DIAMETER MAXIMUM "d"		WALL THICKNESS MINIMUM "W2"	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.
0.4/0.2	0.70±0.20	0.028±0.008	0.10	0.004	0.22	0.009	0.19	0.007
0.6/0.3	0.95±0.25	0.037±0.010	0.10	0.004	0.30	0.012	0.19	0.007
0.8/0.4	1.20±0.25	0.047±0.010	0.10	0.004	0.40	0.016	0.25	0.010
1.0/0.5	1.40±0.25	0.055±0.010	0.10	0.004	0.50	0.020	0.25	0.010
1.5/0.75	1.90±0.25	0.075±0.010	0.10	0.004	0.75	0.030	0.25	0.010
2.0/1.0	2.30±0.25	0.091±0.010	0.10	0.004	1.00	0.039	0.25	0.010
2.5/1.25	2.80±0.25	0.110±0.010	0.15	0.006	1.25	0.049	0.25	0.010
3.0/1.5	3.30±0.25	0.130±0.010	0.15	0.006	1.50	0.059	0.25	0.010
3.5/1.75	3.80±0.25	0.150±0.010	0.15	0.006	1.75	0.069	0.25	0.010
4.0/2.0	4.40±0.25	0.173±0.010	0.15	0.006	2.00	0.079	0.25	0.010
5.0/2.5	5.50±0.25	0.217±0.010	0.15	0.006	2.50	0.098	0.25	0.010
6.0/3.0	6.50±0.40	0.256±0.016	0.15	0.006	3.00	0.118	0.28	0.011
7.0/3.5	7.50±0.40	0.295±0.016	0.15	0.006	3.50	0.138	0.28	0.011
8.0/4.0	8.50±0.40	0.335±0.016	0.15	0.006	4.00	0.157	0.28	0.011
9.0/4.5	9.50±0.40	0.374±0.016	0.15	0.006	4.50	0.177	0.28	0.011
10.0/5.0	10.50±0.50	0.413±0.020	0.15	0.006	5.00	0.197	0.28	0.011

PRODUCT DIMENSIONS  
V4 TUBING DIMENSIONS USA CUSTOMARY

SIZE	AS SUPPLIED		AS RECOVERED			
	INSIDE DIAMETER MINIMUM "D"		INSIDE DIAMETER MAXIMUM "d"		WALL THICKNESS NOMINAL "W2"	
	mm.	in.	mm.	in.	mm.	in.
3/64	1.17	0.046	0.58	0.023	0.30±0.05	0.012±0.002
1/16	1.60	0.063	0.79	0.031	0.30±0.05	0.012±0.002
3/32	2.36	0.093	1.17	0.046	0.30±0.05	0.012±0.002
1/8	3.17	0.125	1.57	0.062	0.33±0.05	0.013±0.002
3/16	4.74	0.187	2.36	0.093	0.33±0.05	0.013±0.002
1/4	6.35	0.250	3.17	0.125	0.36±0.05	0.014±0.002
3/8	9.52	0.375	4.74	0.187	0.36±0.05	0.014±0.002
1/2	12.70	0.500	6.35	0.250	0.36±0.05	0.014±0.002
3/4	19.05	0.750	9.52	0.375	0.46±0.08	0.018±0.003
1	25.40	1.000	12.70	0.500	0.51±0.08	0.020±0.003

### PRODUCT INFORMATION

FLAME RETARDANT

SHRINK RATIO-2:1


COLOUR: BLACK, WHITE, RED, YELLOW, BLUE, GREEN, BROWN, ORANGE, VIOLET AND GREY.

TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZE REFERENCED WITHIN THIS DRAWING.

STANDARD CUTTING TOLERANCES(mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm(Inches)



MATERIAL  
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±0.1  
1 PLC ±0.1  
2 PLC ±0.01  
3 PLC ±0.001  
4 PLC ±0.0001  
ANGLES ±  
FINISH -

DWN	23MAR2023
CHK	BASAVARAJA D A
APVD	23MAR2023
APVD	SELVAPANDIAN B
APVD	MAYO BAKARE
PRODUCT SPEC	RW-3023
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-



NAME VERSAFIT V4 TUBING POLYOLEFIN, FLEXIBLE, HEAT-SHRINKABLE, NON-FLAME-RETARDANT			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	VERSAFIT_V4	-
SCALE	NTS	SHEET	OF
		1	1
REV	AI		