


THREE CONDUCTOR CABLE, RADIATION-CROSSLINKED, POLYALKENE INSULATED, SHIELDED
AND JACKETED, 600 VOLT, 150°C

The complete requirements for procuring the wire described herein shall consist of this document.



Part Description	Nominal Conductor Cross Sectional Area (mm ²)	Component Wire Description	Maximum Resistance @ 20°C (Ohms/km)	Shield Size (mm)	Jacket Thickness (mm)		Overall Diameter (mm)			Maximum Weight (kg/km)
					Min	Nom	Min	Nom	Max	
VG 95218 T023 F006	0.25	VG 95218 T020 A016	87.70	0.13	0.15	0.200	3.02	3.15	3.28	21.40
VG 95218 T023 F004	0.40	VG 95218 T020 A001	54.20	0.13	0.15	0.200	3.43	3.54	3.68	28.00
VG 95218 T023 F005	0.60	VG 95218 T020 A003	34.20	0.13	0.15	0.200	3.86	3.98	4.14	37.20
VG 95218 T023 F014	1.00	VG 95218 T020 A005	21.40	0.13	0.18	0.228	4.42	4.63	4.67	51.30
VG 95218 T023 F015	1.20	VG 95218 T020 A006	16.70	0.13	0.18	0.228	4.80	5.02	5.08	61.10

COLOUR CODE : Component for the above cables shall be VG 95218 T020 AXXX as per table, colour shall be white.
i.e. Components for VG 95218 T023 F006 shall be VG 95218 T020 A016
Jacket colour shall be White.

PERFORMANCE REQUIREMENTS : Shall be tested to the issue in effect of WSD 955.
Shall meet the requirements of the issue in effect of VG 95218 Part 23 Specification for Type F cables.

APPROVAL: Electronic sign off - no signatures will appear.