


TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED,  
600 VOLT AC, 150°C

The complete requirements for procuring the wire described herein shall consist of this document.

**Component wires -**  
VG 95218 T020 AXXX  
See below



Part Description	Nominal Conductor Cross Sectional Area (mm <sup>2</sup> )	Component Wire Description	Maximum Resistance @ 20°C (Ohms/km)	Outside Diameter (mm)		Maximum Weight (kg/km)
				Nom	Max	
VG 95218 T021 E010	0.25	VG 95218 T020 A016	87.70	2.03	2.13	6.80
VG 95218 T021 E001	0.40	VG 95218 T020 A001	54.20	2.39	2.48	9.60
VG 95218 T021 E002	0.60	VG 95218 T020 A003	34.20	2.79	2.90	14.10
VG 95218 T021 E003	1.20	VG 95218 T020 A006	16.70	3.71	3.80	27.20

**COLOUR CODE:**

Components for the above cables shall be VG 95218 T020 AXXX as per table, colour shall be white.  
i.e. Components for VG 95218 T021 E010 shall be VG 95218 T020 A016

**PERFORMANCE REQUIREMENTS :**

Shall be tested to the issue in effect of WSD 955.  
Shall meet the requirements of the issue in effect of VG 95218 Part 21 Specification for Type E cables.

**APPROVAL:**

Electronic sign off - no signatures will appear.