



Engineering Product Design

Product Construction

7 Conductor Cable
Jacketed

Controlled Customer Copy

B.W.B.
GERMANY

Product Description

VG 95218 T027 A002

Rev

2

Designer

Paul Cleary

Date

09/03/2021


Product Manager

Mark Johnstone


Date

09/03/2021

Component Identification



Cross-Section



Components

ID	Type	Quantity	Part Description	(Components refer to issue in effect at date of issue of this EPD)
A	Wire	7	VG 95218-T020-E089	

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A1	9	1		
A2	9	2		
A3	9	3		
A4	9	4		
A5	9	5		
A6	9	6		
A7	9	7		

Cablings

Layer No	Quantity	Description	Nominal O.D. mm
Layer 1	1	VG 95218-T020-E089	
Layer 2	6	VG 95218-T020-E089	6.2

Tyco Electronics UK Ltd.
Faraday Road, Dorcan
Swindon
SN3 5HH
Tel: (01793) 528171
Website: www.te.com

TE Connectivity is a trading name
of Tyco Electronics UK Ltd, which
is registered in England and
Wales, number 550926.
Registered office: Faraday Road,
Dorcan, Swindon, SN3 5HH

This drawing and the information set forth hereon
are the property of Tyco Electronics UK Ltd, and
are to be held in trust and confidence. Publication,
duplication, disclosure or use for any purpose not
expressly authorised in writing by Tyco Electronics
UK Ltd is prohibited.

© 2021 Tyco Electronics UK Limited.
A TE Connectivity Ltd company.
All Rights Reserved.



Engineering Product Design

Product Construction	Controlled Customer Copy	Product Description	Rev
7 Conductor Cable Jacketed	B.W.B. GERMANY	VG 95218 T027 A002	2

Outer		
Layer Type	Description	Nominal O.D. mm
Wrap:	Polyester	6.3
Jacket: Extrusion 1	Zerohal® - Black Marked 'Raychem - VG 95218 T027 A002 - K1010 - VDE Reg.Nr. 7094'	8.3 ±0.3 Min Wall - 0.79mm

Cable Characteristics	
Calculated Maximum Weight	159 (kg/km)
This cable is RoHS Compliant	

Specifications
VG 95218 Part 27 Type A

Notes
Internal reference - EPD87256A

Lengths
Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths with no single length less than 25m:

Order Quantity (m) + One other length
100