





Engineering Product Design

Product Construction 3 Conductor Cable Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T027 A008	Rev 2
--	--	---	-----------------

Designer <i>Paul Cleary</i>	Date 11/03/2021	Product Manager <i>Mark Johnstone</i>	Date 11/03/2021
---------------------------------------	---------------------------	---	---------------------------

Component Identification

Cross-Section



Components

ID	Type	Quantity	Part Description	(Components refer to issue in effect at date of issue of this EPD)
A	Wire	1	VG 95218-T020-E081	
B	Wire	1	VG 95218-T020-E086	
C	Wire	1	VG 95218-T020-E08G	

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A1	1			
B1	6			
C1	45			

Cabling

Layer No	Quantity	Description	Nominal O.D. mm
Layer 1	1	VG 95218-T020-E081	4.5
	1	VG 95218-T020-E086	
	1	VG 95218-T020-E08G	



Engineering Product Design

Product Construction 3 Conductor Cable Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T027 A008	Rev 2
--	--	---	-----------------

Layer Type	Description	Nominal O.D. mm
Wrap:	Polyester	4.6
Jacket: Extrusion 1	Zerohal® - Black Marked 'Raychem - VG 95218 T027 A008 - K1010 - VDE Reg.Nr. 7094'	6.8 ±0.3 Min Wall - 0.83mm

Cable Characteristics	
Calculated Maximum Weight	85 (kg/km)
This cable is RoHS Compliant	

Specifications
VG 95218 Part 27 Type A

Notes
Internal reference - EPD92384A

Lengths
Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths with no single length less than 25m:

Order Quantity (m) + One other length
100