





Engineering Product Design

Product Construction 14 Conductor Cable Shielded and Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T028 C056	Rev 2
--	--	---	-----------------

Designer <i>John Ribbons</i>	Date 16/07/2019	Product Manager <i>Mark Johnstone</i>	Date 16/07/2019
--	---------------------------	---	---------------------------

Component Identification

Cross-Section



Components

ID	Type	Quantity	Part Description
A	Cable	1	VG 95218 T023 G004
B	Cable	2	VG 95218 T023 G005
C	Cable	4	VG 95218 T023 G006

Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A1	0/1			
B1	0/6			
B2	0/6			
C1	0/8			
C2	0/8			
C3	0/8			
C4	0/8			



Engineering Product Design

Product Construction 14 Conductor Cable Shielded and Jacketed	Controlled Customer Copy B.W.B. GERMANY	Product Description VG 95218 T028 C056	Rev 2
--	--	---	-----------------

Cabling

Layer No	Quantity	Description	Nominal O.D. mm
Layer 1	1	VG 95218 T023 G005	
Layer 2	1	VG 95218 T023 G004	
	1	VG 95218 T023 G005	
	4	VG 95218 T023 G006	
	6	Fillers	9.1

Outer

Layer Type	Description	Nominal O.D. mm
Wrap:	Polyester	9.2
Shield: Optimised Braid	Tin Plated Copper	9.9
Jacket: Extrusion 1	Zerohal® - Black Marked 'Raychem - VG 95218 T028 C056 - K1010 - VDE Reg.Nr. 7095 - LFMSGSGO(7x2x0.4)'	11.8 ±0.5 Min Wall - 0.80mm

Cable Characteristics

Maximum Weight	263 (kg/km)
Maximum Surface Transfer Impedance	45 milli Ohms/metre @ 30MHz 30 milli Ohms/metre @ 10MHz

This cable is RoHS Compliant

Specifications

VG 95218 Part 28 Type C

Notes

Braid - AWG34
Internal reference - EPD94266A

Lengths

Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths with no single length less than 25m:

Order Quantity (m) + One other length
100