



# Engineering Product Design

## Product Construction

19 Conductor Cable  
Shielded and Jacketed

## Controlled Customer Copy

B.W.B.  
GERMANY

## Product Description

**VG 95218 T028 D077**

## Rev

2

## Designer

*Paul Cleary*

## Date

16/02/2021


## Product Manager

*Mark Johnstone*


## Date

16/02/2021

## Component Identification



## Cross-Section



## Components

ID	Type	Quantity	Part Description	(Components refer to issue in effect at date of issue of this EPD)
A	Wire	19	VG 95218-T020-A002	

## Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A1	9	1		
A2	9	2		
A3	9	3		
A4	9	4		
A5	9	5		
A6	9	6		
A7	9	7		
A8	9	8		
A9	9	9		
A10	9	10		
A11	9	11		
A12	9	12		



# Engineering Product Design

Product Construction	Controlled Customer Copy	Product Description	Rev
19 Conductor Cable Shielded and Jacketed	B.W.B. GERMANY	<b>VG 95218 T028 D077</b>	2

## Component Identification

Key	Wire/Core Colour(s)	Wire/Core Number(s)	Jacket/Wrap Colour(s)	Jacket/Wrap Number
A13	9	13		
A14	9	14		
A15	9	15		
A16	9	16		
A17	9	17		
A18	9	18		
A19	9	19		

## Cabling

Layer No	Quantity	Description	Nominal O.D. mm
Layer 1	1	VG 95218-T020-A002	
Layer 2	6	VG 95218-T020-A002	
Layer 3	12	VG 95218-T020-A002	6.5

## Outer

Layer Type	Description	Nominal O.D. mm
Shield: Optimised Braid	Tin Plated Copper - Tinel	7.1
Jacket: Extrusion 1	FDR 25 - Black Marked 'Raychem - VG 95218 T028 D077 - K1010 - VDE Reg. Nr. 9425'	9.7 ±0.5 Min Wall - 1.01mm

## Cable Characteristics

Calculated Maximum Weight	195 (kg/km)
Maximum Surface Transfer Impedance	70 milli ohms/metre @ 30MHz
This cable is RoHS Compliant	

## Specifications

VG 95218 Part 28 Type D

## Notes

Braid - AWG 36  
Internal reference - EPD42627A

## Lengths

Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths with no single length less than 25m:

Order Quantity (m) + One other length  
100

Tyco Electronics UK Ltd.  
Faraday Road, Dorcan  
Swindon  
SN3 5HH  
Tel: (01793) 528171  
Website: www.te.com

TE Connectivity is a trading name of Tyco Electronics UK Ltd, which is registered in England and Wales, number 550926.  
Registered office: Faraday Road, Dorcan, Swindon, SN3 5HH

This drawing and the information set forth hereon are the property of Tyco Electronics UK Ltd, and are to be held in trust and confidence. Publication, duplication, disclosure or use for any purpose not expressly authorised in writing by Tyco Electronics UK Ltd is prohibited.

© 2021 Tyco Electronics UK Limited.  
A TE Connectivity Ltd company.  
All Rights Reserved.