



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		ECR-24-199903	29JAN2024	YB	AK

LABEL AND LINER DESIGN



PRESENTATION



LABELS PER ROLL: 5 000
LABELS ACROSS: 2

OUTSIDE WOUND

TE PN: F77529-000

All dimensions in mm [INCHES]

- Kiss cut
- Back slit
- Perforation
- 2 kiss cut enductions
- Die cut
- Adhesive cut
- 45° die cut

Grid removed: Yes
Sales unit: The label

PRINTING	
Color	Color
1 N.A.	5
2	6
3	7
4	8

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

DIMENSIONS:	
mm [inches]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	± -

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DWN	29JAN2023
CHK	29JAN2023
APVD	30JAN2023
PRODUCT SPEC	A. KEAN
APPLICATION SPEC	TTDS-073
WEIGHT	0.02 g

MATERIAL		WHITE POLYESTER	
ADHESIVE TYPE		PERMANENT	
LINER		GLASSINE PAPER	
TE Connectivity		Part Description	
WP-381191-5-9		-	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	FB1U7	C=F77529-000	-
SCALE	NTS	SHEET	1 OF 1
REV	G		

F77529-000