



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	22JAN2024	AN	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (NOM) (W)	
	mm.	in.	mm.	in.	mm.	in.
03	7.62	0.300	2.54	0.100	2.03	0.080
04	10.16	0.400	3.81	0.150	2.03	0.080
07	19.05	0.750	5.59	0.220	2.03	0.080
11	27.94	1.100	9.53	0.375	2.79	0.110
15	38.10	1.500	12.70	0.500	3.05	0.120
20	50.80	2.000	19.05	0.750	3.05	0.120
30	76.20	3.000	31.75	1.250	4.06	0.160
40	101.60	4.000	44.45	1.750	4.06	0.160


PRODUCT INFORMATION:

1. FLAME RETARDANT
2. MATERIAL: IRRADIATED MODIFIED POLYOLEFIN  
STANDARD COLOUR: BLACK
3. SHRINK RATIO 3:1
4. LONGITUDINAL CHANGE +1 TO -10%
5. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	±0.1
1 PLC	±0.1
2 PLC	±0.01
3 PLC	±0.001
4 PLC	±0.0001
ANGLES	±
FINISH	-

MATERIAL -

DWN	22JAN2024	AYESHABANU N
CHK	22JAN2024	BASAVARAJA D A
APVD	22JAN2024	VLADIMIR NEMEC
PRODUCT SPEC	RW-2016	
APPLICATION SPEC	114-120031	
WEIGHT	-	
CUSTOMER DRAWING		



NAME XFFR-TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-XFFR_TUBING	-

SCALE NTS SHEET 1 OF 1 REV A