# THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP SHANGHAI LTD

# APPLICATION SPECIFICATION 114-115031

### 1.0MM PITCH WTB CONNECTOR

# 1. SCOPE

This specification covers the requirements for crimping of 1.0mm pitch WTB Connector for applicator and manually operated hand tool.


# 2. APPLICABLE PRODUCTS


This instruction sheet is applicable to products shown below:

Part No.	Description	Wire Size	Conductor OD
2367199-*	1.0mm WTB Contact		
*-2367196-*	1.0mm WTB RIGHT ANGLE TYPE WITH LATCH	AWG #28	$7/0.127 \pm 0.007$
*-2367197-*	1.0mm WTB Side Vertical Type With Latch		Ø0.38
*-2367198-*	1.0 WTB HOUSING WITH LATCH		

### 3. CRIMPING DATA

Contact	Wire Size			Crimp H	leight (mm)	Crimp Width (mm)		
Part No.	UL Style (REF.)	Size (AWG)	Insulation OD(mm)	Conductor A	Insulation B	Conductor W1	Insulation W2	
2367199-*	UL3302	#28	0.62±0.05	0.44~0.48	1.0±0.05	$0.73 \pm 0.05$	0.70±0.1	







Strip length: 1.3~1.6mm ref.

				DR Jone Ji CHK Wenke He		TE Connectivity AMP Shanghai Ltd			d
				APP Wenl	ке Не	NO 114-115031		<b>REV</b> 2	LOC EC
2	REVISED	J.J	30MAY		1.0MM PITCH WTB CONNECTOR				
LTR	REVISION RECORD	DR	DATE	1 of 3					

# 4. NOMENCLATURE






connectivity	TE Connectivity	PAGE	NO	REV	LOC
	AMP Shanghai Ltd	2	114-115031	2	ES

# 5. CRIMPING REQUIREMENT


No.		Check Items	Crimping Requirements Applicator	Remarks
1	7	Wire Strip Length	1.3~1.6 mm	Refer to ① of Fig.1
2	Wire-	End Protrusion Length	0.05 ~ 0.25 mm	Refer to ② of Fig.1
3	Cı	ut-Off Tab Length	0.2 mm Max.	Refer to ③ of Fig.1
4	Bellmout	Front	Presence of Front Bellmouth is optional	Refer to ④ of Fig.1
		Rear	0.1 ~ 0.3 mm	Refer to ⑤ of Fig.1
5	v	Wire Barrel Crimp	Refer Table1	Refer to 6 of Fig.1
6	Inst	ulation Barrel Width	0.80mm Max	Refer to 7of Fig.1
7	Insulati	ion Barrel Crimp Height	Refer Table 1	Refer to ® of Fig.1
8		Bend-Up	6° Max.	
9		Bend-Down	6° Max.	
10	Allowabl e Deviation after Crimping	Twisting	5° Max.	
11		Rolling	5° Max.	

TE Connectivity AMP Shanghai Ltd  PAGE NO 3 114-115031  REV LOC ES
--

### 6. STANDARD INSULATION CRIMPING



# 7. CONDUCTORS CRIMPING CONDITION



TE Connectivity AMP Shanghai Ltd	PAGE 4	NO 114-115031	REV 2	LOC ES	
----------------------------------	-----------	------------------	-------	-----------	--