

#### PRODUCT DESCRIPTION

The Mini-Universal MATE-N-LOK Connector System offers wire-to-wire and wire-to-board connections with contacts on a 4.14 mm [.163] centerline and current ratings up to 9.5 Amps max. per line. Plug and receptacle housings allow wire-to-wire and wire-to-panel configurations and header assemblies offer wire-to-board connections in vertical and right angle configurations. Wire-to-wire, free-hanging or panel mount options are available in 1-15 position in-line, dual row or matrix configurations and wire-to-board systems in dual row and matrix configurations are available in 2-24 positions. Hermaphroditic housings are also available in 2-4 positions for free-hanging applications. Crimp, snap-in pin and receptacle contacts are used to terminate 30-16 [0.05-1.2 mm²] AWG wire with insulation diameters up to 3.20 mm. The Mini-Universal MATE-N-LOK Connector System also offers a splash-proof design allowing for use in areas where high humidity, intermittent liquid splashing or foam-in applications require a sealed connector for improved electrical performance. The sealed system is available in select 2-16 positions.

## **INDUSTRIES**

- Household appliances
- Indoor and outdoor lighting
- Medical equipment
- Security systems
- Industrial controls
- HVAC system controls
- Storage and networking systems

## **FEATURES AND BENEFITS**

- Discrete wire interconnect available in 1-24 position
- wire-to-wire and wire-to-board pin and receptacle connector system
- Contacts are on 4.14 mm centerline spacing
- Contacts are available in strip form or loose piece
- Pins and sockets can be accommodated in the same housing
- · Vertical and right angle pin headers
- Splash-proof design for applications that require sealing
- UL, CSA & VDE approved

#### CONTACTS

Wire Size Range		Plat	ing	P	in	Socket			Semiautomatic		Hand Tool
AWG	Ins. Dia. Range	Pre-Tin	Gold	Strip From	Loose Piece	Strip From	Loose Piece	Automatic	K Press	G Press	part no.
30-26 [.0512]	.035050 [.889-1.27]	×		770835-1	794059-1	770834-1	794058-1	567418-1	567418-2	567418-3	90717-2
30-26 [.0512]	.035050 [.889-1.27]		x	1-770835-0	1-794059-0	1-770834-0	1-794058-0	567418-1	567418-2	567418-3	90717-2
26-22 [.123]	.047069 [1.19-1.75]	×		770901-1*	770985-1*	770702-1*	770986-1*	567066-1	567066-2	567418-3	91529-1
26-22 [.123]	.047069 [1.19-1.75]		X	1-770901-0*	1-770985-0*	1-770902-0*	1-770986-0*	567066-1	567066-2	567418-3	91529-1
22-18 [.38] or 22 x (2) [.3]	.059094 [1.50-2.39] or 0.67 x (2) [3.38]	×		770903-1*	770987-1*	770904-1*	770988-1*	567067-1	567067-2	567067-3	91522-1
22-18 [.38] or 22 x (2) [.3]	.059094 [1.50-2.39] or 0.67 x (2) [3.38]		×	1-770903-0*	1-770987-0*	1-770904-0*	1-770988-0*	567067-1	567067-2	567067-3	91522-1
20-16 [.512] or 20 x (2) [.5]	.079126 [2.01-3.20] or .075 x (2) [1.91]	×		794406-1	171638-1	794407-1	171639-1	680582-1	680582-2	680582-3	91536-1
20-16 [.512] or 20 x (2) [.5]	.079126 [2.01-3.20] or .075 x (2) [1.91]		x	1-794406-0		1-794407-0		680582-1	680582-2	680582-3	91536-1
22-26	.050069 [1.27-1.75]	×		770901-1	770985-1	770902-1	770986-1				
22-26	.050069 [1.27-1.75]		X	1-770901-0	1-770985-0	1-770902-0	1-770986-0				
18-22	.050083 [1.27-2.11]	×		794406-1		794831-1					
18-22	.050083 [1.27-2.11]		х	794406-3		794831-3					
16	.050083 [1.27-2.11]	×		1586537-1		1586538-1					
16	.050083 [1.27-2.11]		X	-		1586538-3					

 $<sup>^{\</sup>ast}\text{Can}$  be used in conjunction with individual wire seal - part no. 794758-1

Contact Extraction Tool Part No. 189727-1

Contact Insertion Tool Part No. 91002-1





The Mini-Universal MATE-N-LOK contacts are brass with pre-tin or gold plating. See catalog 82181 for additional available options. The contacts are fully protected in the housings. The pins and sockets can be accommodated in the same housing.

Pin Socket

#### **CAP HOUSINGS**

UL94V-0		UL9	Configurations				
No. of Circuits	Panel Mount	Free-Hanging	Panel Mount	Free-Hanging	Single Row	Dual Row	Matrix
1		172156-1		172327-1	×		
2	172157-1	172233-1	172328-1	172343-1	×		
3	172158-1	172234-1	172329-1	172344-1	×		
4		172159-1		172330-1		×	
6		172160-1		172331-1		×	
9		172161-1		172332-1			х
12		172162-1		172333-1			х

#### **HERMAPH RODITIC HOUSINGS**

No. of Circuits	UL94V-0 Nylon, White Color	UL94V-2, Natural Color
2	173956-1	172807-1
3	173957-1	172808-1
4	173958-1	172809-1

**Note:** Housing mates to itself; 2 required per wire-to-wire connection



**Cap Housing** 

## **VERTICAL PIN HEADERS**

	Vertical					_	
No. of Circuits	With Drain Holes	W/out Drain Holes	In Line	Dual Row	Matrix	Tin	Gold
2	1-770166-0	1-770872-0	×			×	
2	1-770166-1	1-770872-1	×				×
3	1-770170-0	1-770873-0	×			×	
3	1-770170-1	1-770873-1	×				х
4	1-770174-0	1-770874-0		×		×	
4	1-770174-1	1-770874-1		×			×
6	1-770178-0	1-770875-0		×		×	
6	1-770178-1	1-770875-1		×			×
8	1-794065-0	1-794073-0		×		×	
8	1-794065-1	1-794073-1		×			×
9	1-770182-0	1-770976-0			×	×	
9	1-770182-1	1-770976-1			×		×
10	1-770743-0	1-770858-0		×		×	
10	1-770743-1	1-770858-1		×			×
12	1-794066-0	1-770621-0		×		×	
12	1-794066-1	1-770621-1		×			×
12	1-770186-0	1-794040-0			х	×	
12	1-770186-1	1-794040-1			×		×
14	1-794067-0	1-794074-0		×		×	
14	1-794067-1	1-794074-1		×			×
15	1-770190-0	1-770859-0			×	×	
15	1-770190-1	1-770859-1			×		×
16	1-794068-0	1-794075-0		×		×	
16	1-794068-1	1-794075-1		×			×
18	1-794069-0	1-794076-0		×		×	
18	1-794069-1	1-794076-1		×			×
20	1-794070-0	1-794077-0		×		×	
20	1-794070-1	1-794077-1		×			×
22	1-794071-0	1-794078-0		×		×	
22	1-794071-1	1-794078-1		×			х
24	1-794072-0	1-794079-0		×		×	
24	1-794072-1	1-794079-1		×			×



**Vertical Pin Header** 

# RIGHT ANGLE HEADERS

No. of Circuits	Part No.	In Line	Dual Row	Gold	Tin
1	1-794374-0				×
1	1-794374-1			×	
2	1-770966-0	×			×
2	1-770966-1	×		×	
3	1-770967-0	×			×
3	1-770967-1	×		×	
4	1-770968-0		×		×
4	1-770968-1		х	×	
6	1-770969-0		×		×
6	1-770969-1		х	×	
8	1-770970-0		×		×
8	1-770970-1		×	×	
10	1-770971-0		×		X
10	1-770971-1		×	×	
12	1-770972-0		×		X
12	1-770972-1		×	×	
14	1-770973-0		×		х
14	1-770973-1		x	×	
16	1-770974-0		x		х
16	1-770974-1		x	×	
18	1-794105-0		x		х
18	1-794105-1		x	×	
20	1-794106-0		×		x
20	1-794106-1		×	×	
22	1-794107-0		×		×
22	1-794107-1		×	×	
24	1-794108-0		×		×
24	1-794108-1		х	×	



**Right Angle Pin Header** 

#### **VERTICAL PC BOARD BLINDMATE PIN HEADERS**

No. of Circuits	Part No. w/ Drain Holes	Dual Row	Matrix	Tin	Gold
4	1-794325-0	×		×	
4	1-794325-1	×			×
6	1-794326-0	×		×	
6	1-794326-1	×			×
8	1-794327-0	×		×	
8	1-794327-1	×			×
9	1-794432-0		×	×	
9	1-794432-1		×		×
10	1-794328-0	×		×	
10	1-794328-1	×			×
12	1-794329-0		×	×	
12	1-794329-1		×		×
15	1-794330-0		×	×	
15	1-794330-1		×		×



**Vertical PC Board Pin Header** 

#### **GANG SEALS**

No. of Circuits	Interface Seals	Gang Wire Seal	Plug for Sealing	Cap for Sealing	Vertical Headers for Sealing*	Right Angle Headers for Sealing*
2	794772-2	1586359-2	794894-1	794896-1	1-770872-x	1-770966-x
4	794772-4	1586359-4	794805-1	794939-1	1-770874-x	1-770968-x
6	794772-6	1586359-6	794895-1	794940-1	1-770875-x	1-770969-x
8	794772-8	1586359-8	794821-1	794941-1	1-794073-x	1-770970-x
10	1-794772-0	1-1586359-0	794781-1	794942-1	1-770858-x	1-770971-x
16	1-1586362-6	1-1586359-6	794824-1		1-794075-x	1-770974-x



Single & Gang Wire Seals with Interfacial Seal



Single Wire Seal



**Gang Seal** 



Single Wire Seal




**Wire Seal Configuration** 


#### **PLUG HOUSINGS**

No. of Circuits	UL94V-0	UL94V-2	Single Row	Dual Row	Matrix
1	172164-1	172335-1	×		
2	172165-1	172336-1	×		
3	172166-1	172337-1	×		
4	172167-1	172338-1		x	
6	172168-1	172339-1		×	
8	770579-1	-		×	
9	172169-1	172340-1			×
10	770580-1	-		x	
12	172170-1	172341-1			х
12	770581-1	-		X	
14	770582-1	-		x	
15	172171-1	172342-1			х
16	770583-1	-		X	
18	770584-1	-		x	
20	770585-1	-		×	
22	770586-1	-		x	
24	770587-1	-		×	

#### **STRAIN RELIEFS - PLUG OR CAP HOUSINGS**

No. of Circuits	Wire Bundle Dia. Range	UL94V-0 Part No.	Use with:	Dual Row	Matrix
6	.135220, 4.19-5.59	794423-1	172168-1, 172160-1, 172339-1, 172331-1	×	
8	.180245 ,4.57-6.22	794370-1	770979-1	×	
9 Plug		316454-1	172169-1, 172340-1		×
9 Cap		316455-1	172161-1, 171232-1		х





#### **CONNECTOR KITS**

Kit Part Number	Description
1-2110832-0	Mini-Universal MATE-N-LOK Panel Mount Plug and Receptacle Kit
1-2110832-1	Mini-Universal MATE-N-LOK Vertical Header and Plug Connector Kit
1-2110832-2	Mini-Universal MATE-N-LOK Right Angle Header and Plug Connector Kit
1-2110832-3	Mini-Universal MATE-N-LOK Plug and Receptacle Connector Kit
1-2110832-5	Mini-Universal MATE-N-LOK Deluxe Header, Plug, Receptacle and Sealed Components Kit
1-2110832-7	Mini-Universal MATE-N-LOK and Universal MATE-N-LOK Deluxe Sealed Plug, Receptacle and Components Kit
1-2110832-8	Mini-Universal MATE-N-LOK, Universal MATE-N-LOK and Universal MATE-N-LOK II Deluxe Plug and Receptacle Connector Kit

#### QUESTIONS THAT WILL HELP YOU BETTER SELECT THE PRODUCT THAT YOU NEED:

# What are the current and voltage requirements for your application?

The Mini-Universal MATE-N-LOK connector system has a maximum current rating of 9.5 Amps per line and is rated for 600 Volts AC/DC.

#### What are the wire type and size requirements?

The Mini-Universal MATE-N-LOK connector system contacts are approved for use with 4 different wire ranges from 30 AWG [0.05] to 16 AWG [1.20] wire with a maximum insulation diameter of .126 [3.20].

#### What are the number of positions?

The Mini-Universal MATE-N-LOK connector system is available in wire-to-wire, free-hanging or panel mount options in 1-15 position in-line, dual row or matrix configurations and wire-to-board is available in 2-24 positions dual row and matrix configurations. The hermaphroditic housings are available in 2-4 positions for freehanging applications and the sealed system is available in select 2-16 positions.

#### What are the operating temperature requirements?

The Mini-Universal MATE-N-LOK connector system has a maximum operating temperature of 105°C. For more information regarding operating temperatures refer to product specification 108-1542.

#### What is the benefit of using the hermaphroditic housings?

The Mini-Universal MATE-N-LOK connector system offers a special hermaphroditic housing design where 2 of the same housings in the same position size mate to one another. The benefit of this design simply reduces the amount of part numbers and inventory for the user.

# What is the benefit of using the Mini-Universal MATE -N-LO K Sealed Connector System?

The Mini-Universal MATE-N-LOK Sealed Connector System offers a splash-proof design for use in areas where high humidity, intermittent liquid splashing or foam-in applications require a sealed connector for improved electrical performance. The sealed system is available in select 2-16 positions and requires either individual or ganged wire seals and an interface seal in conjunction with the plug and cap housings uniquely designed to accommodate these seals. The sealed plug housings with wire and interface seal can also be mated to the standard Mini-Universal MATE-N-LOK headers without drain holes for a sealed wire to board application.

Part numbers in this brochure are RoHS Compliant\*, unless marked otherwise. \*as defined www.te.com/leadfree

#### te.com

MATE-N-LOK, TE, TE Connectivity and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However,

TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of

 ${\sf TE}\ \bar{\sf Connectivity}\ products\ should\ make\ their\ own\ evaluation\ to\ determine\ the\ suitability\ of\ each\ such\ product\ for\ the\ specific\ application.$ 

© 2023 TE Connectivity Ltd. family of companies. All Rights Reserved.

02/23 Original

#### FOR MORE INFORMATION

#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK. +44 (0) 800-267666 +33 (0) 1-3420-8686 Netherlands: +31(0)73-6246-999 China: +86 (0) 400-820-6015

