





FEATURES

- Dual-in-Line Package
- 0°C to 50°C Compensated Temperature Range
- ±0.1% Non-Linearity
- 1.0% Interchangeable Span (provided by current set resistor)
- Solid State Reliability

APPLICATIONS

- Medical Instruments
- Airspeed and Altitude Measurements
- Process Control
- Factory Automation
- Vacuum Measurement
- Handheld Calibrators

1220

Standard

SPECIFICATIONS

- PC Board Mountable Pressure Sensor
- 0-50 mV Output
- Voltage Excitation
- Gage, Absolute, and Differential
- Temperature Compensated

The 1220 is a temperature compensated, piezoresistive silicon pressure sensor packaged in a dual-in-line configuration and intended for cost sensitive applications where excellent performance and long-term stability are required.

When using the 1220 with a fixed voltage reference and current set resistor as shown in the application schematic, a span of 50mV and 1% interchangeability can be achieved. Integral temperature compensation is provided over a range of 0-50°C using laser-trimmed resistors. Gage, absolute, and differential pressure ranges from 0-2 psi to 0-100 psi are available. Multiple lead and tube configurations are available for specific applications.

Please refer to the 1220 1psi datasheet for low pressure applications. For current excitation, please refer to the Model 1210.

STANDARD RANGES

Range	psia	psid	psig
0 to 2		•	*
0 to 5		•	*
0 to 15	•	•	*
0 to 30	•	•	*
0 to 50	•	•	*
0 to 100	•	•	•

PERFORMANCE SPECIFICATIONS

Supply Voltage: See application schematic

Ambient Temperature: 25°C (unless otherwise specified)

PARAMETERS	MIN	ТҮР	МАХ	UNITS	NOTES		
Span	49.5	50	50.5	mV	1		
Zero Pressure Output	-2		2	mV			
Pressure Non Linearity	-0.1	±0.05	0.1	%Span	2		
Pressure Hysteresis	-0.1	±0.01	0.1	%Span			
Input Resistance	2500	4400	6000	Ω			
Output Resistance		4200		Ω			
Temperature Error – Span	-0.5	±0.3	0.5	%Span	3		
Temperature Error – Zero	-0.5	±0.1	0.5	%Span	3,8		
Temperature Coefficient-Resistance		.15		%/°C	3		
Thermal Hysteresis – Zero		±0.05		%Span	3		
Short Term Stability (Offset & Span)		±0.05		% Span	4		
Long Term Stability (Offset & Span)		±0.10		% Span	5		
Supply Voltage Reference		1.235		V			
Response Time (10% to 90%)		1.0		ms	6		
Output Noise (10Hz to 1kHz)		1.0		μV p-p			
Pressure Overload			3X	Rated	7		
Compensated Temperature	0		50	°C			
Operating Temperature	-40		+125	°C			
Storage Temperature	-50		+150	°C			
Weight		3		grams			
Solder Temperature	250ºC Max 5 Sec.						
Weight	Non-Corrosive Dry Gases Compatible with Silicon, Pyrex,						

RTV, Ceramic, Nickel, Gold, and Aluminum

Notes

1. Refer to application schematic.

2. Best fit straight line.

3. Maximum temperature error between 0°C and 50°C with respect to 25°C. For 2psi devices, Temperature Error -- Zero is ±1.25%.

4. Short term stability over 7 days with constant current and temperature.

5. Long term stability over a one year period with constant voltage and temperature.

6. For a zero-to-full scale pressure step change.

7. 2X maximum for 100 psi device.

DIMENSIONS



CONNECTIONS



APPLICATION SCHEMATIC



ORDERING INFORMATION



NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752

EUROPE

Measurement Specialties (Europe), Ltd., a TE Connectivity Company Tel: 800-440-5100 customercare.bevx@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 mailto:customercare.shzn@te.com

customercare.frmt@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

