



# **CeeLok FAS-T CONNECTORS**

10 GB/S ETHERNET CONNECTIVITY . . . COMPACT . . . RUGGED . . . RELIABLE



10 Gb/s ethernet connectivity . . . compact . . . rugged . . . reliable



#### **HIGH SPEED**

- Gigabit or 10 Gigabit rates
- Compatible with Cat 5e, Cat 6a or Cat 7 cables
- T-shaped pin pattern improves signal integrity through uniform crosstalk cancellation

#### **SPACE AND WEIGHT SAVINGS**

• Compact size 8 shell

# EASY TERMINATION AND FIELD REPAIRABILITY

• Crimp-snap, 39029-style contacts

# FLEXIBLE BACKSHELL/ SHIELDING OPTIONS

- Backshell integrated in plug body provides low profile, low cost, low weight strain relief and EMI protection
- Compatible with multiple braid termination techniques, adapter styles and seal boots

#### **RUGGED**

- Scoop-proof design
- Insert assembly mechanically retained for ≤25 lb. retention force
- Robust coupling ring mechanism

CeeLok FAS-T connectors offer a small form factor, field terminable I/O connector capable of 10 Gb/s Ethernet. Crimp-snap contacts enable easy termination and field repairability. The integral backshell offers easy 360-degree shield termination.

The compact size 8 shell helps designers meet the needs of reduced SWaP (size, weight, and power).

The connector's T-shaped contact pattern provides noise cancellation and decoupling to minimize crosstalk and increase signal integrity.

The CeeLok FAS-T connector is a true 100-ohm impedance connector that is compatible with Cat 5e and Cat 6a cables and protocols ranging from the USB and IEEE 1394 to gigabit and 10G Ethernet.









## Performance Characteristics

#### **DATA RATES**

• Gigabit and 10 Gigabit Ethernet when used with Cat 5e, Cat 6a or Cat 7 cables

#### **ELECTRICAL**

- Insulation Resistance: 5000 M $\Omega$  ambient, 1000 M $\Omega$  @ 175°C
- Dielectric Withstanding Voltage: 500 VAC @ sea level 100 VAC @ 70,000 ft.
- Shielding Effectiveness: per MIL-DTL-38999
- Shell-to-Shell Conductivity: 5 mV initial, 10 mV final

#### **MECHANICAL**

- **Vibration, Sine:** MIL-DTL-38999 Series III (60 g), 4 hrs per axis, no elevated temperature
- Vibration, Random: EIA-364-28 Condition VI Letter J (43.92 g)
   Durability: 500 mating cycles
   Contact Retention: 10 lb. min.
   Coupling Torque: 8 in-lb. max.

#### **ENVIRONMENTAL PROPERTIES**

- Operating Temperature: -65°C to +175°C
   Sealing: Altitude immersion: 70,000 ft. (mated condition)
- IP67: Mated condition
- IPX6 (water jet): Receptacle, panel mounted (unmated condition)
- Corrosion Resistance: 500 hr. salt mist

#### **MATERIALS**


- **Shell:** Electroless nickel for DOD-approved, RoHS-compliance, corrosion resistance (500 hr salt mist)
- **Insert:** High-temperature thermoplastic for excellent temperature endurance
- Low dielectric constant for superior signal integrity
- Contacts: Beryllium copper alloy

#### STANDARDS AND SPECIFICATIONS


- Product Specification: 108-2482
  Application Specification: 114-32025
  Instruction Sheet: 408-32046
  Test Report: 501-134002
- Electrical Performance Report: 505-116000









CeeLok FAS-T Differential Return Loss



CeeLok FAS-T Differential NEXT

Four Mated Pairs: 40M Total





CeeLok FAS-T Differential Insertion Loss

# CeeLok FAS-T Connectors

	Contacts Included	Key	Part No.		
Type			Electroless Nickel	Black Zinc Nickel	
		N	2102353-1	2102353-2	
	Socket	A	2102353-3	2102353-4	
Plug		В	2102353-5	2102353-6	
		N	2102353-7	2102353-8	
	None	A	2102353-9	1-2102353-0	
		В	1-2102353-1	1-2102354-2	
		N	2102352-1	2102352-2	
	Pin	A	2102352-3	2102352-4	
Danastaala		В	2102352-5	2102352-6	
Receptacle		N	2102352-7	2102352-8	
	None	Α	2102352-9	1-2102352-0	
		В	1-2102352-1	1-2102352-2	
		N	2102343-1	2102343-2	
	Pin	A	2102343-3	2102343-4	
Box-Mount		В	2102343-5	2102343-6	
Receptacle		N	2102343-7	2102343-8	
	None	A	2102343-9	1-2102343-0	
		В	1-2102343-1	1-2102343-2	
Box-Mount Receptacle, PC Tail	Pin	N	2102453-1	2102453-2	
	Pin	Α	2102453-3	2102453-4	
	Pin	В	2102453-5	2102453-6	
Jam Nut Receptacle, PC Tail	Pin	N	2102351-1	2102351-2	
	Pin	Α	2102351-3	2102351-4	
	Pin	В	2102351-5	2102351-6	

#### Contacts

	Part No.		
Wire Size	Pin	Socket, Hooded	
24 – 26 AWG	2102349-3	2102350-5	

#### **Application Tooling**

Hand Crimp Tool:


M22520/2-01

Crimp Positioner:

TE Part No. 2217375-1


Insertion/Extraction Tool:

TE Part No. 2217376-1




#### **PRODUCT DIMENSIONS**

**Boxmount Receptacle Kit Assembly** Part No. 2102343




Jam Nut Receptacle Assembly, PC Tail Part No. 2102351




# CeeLok FAS-T Connectors

#### **PRODUCT DIMENSIONS**


Receptacle Kit Assembly Part No. 2102352






#### **PRODUCT DIMENSIONS**

**Boxmount Receptacle Assembly, PC Tail** Part No. 2102453




#### **PRODUCT DIMENSIONS**

**Protective Cover Cap, Plug** 



# **Protective Cover Cap, Receptacle**

Part No. 2221478-x



#### **ACCESSORIES**

#### **SolderSleeve Shield Terminators**



#### **Convenient and Effective**

- Terminates a ground lead to cable shield in order to ground the shield
- Simple, quick termination
- Available with and without pigtails

#### **Versatile**

- Center or end strip for ease of termination
- Handles wide range of high data rate cables and diameters

#### **Environmental**

- Operating temperature:
   -55°C to +200°C
- Environmentally sealed
- Mechanically robust

#### **Physical or Other Properties**

- Terminates tin, silver and nickel flat or round braids
- Provides 360° of shielding

#### **Product Offering**

 Contact TE for a complete listing of SolderSleeve shield terminators

#### **CRES-Lock Bandstraps**



#### Easy to Use

 Quick, easy, cost-effective and reliable termination of braided shielding

#### **High Performance**

• Low profile, one-piece design eliminates EMI leakage paths

#### Rugged

 Shock, vibration and environmental tested to meet aerospace and defense requirements

#### **Electrical**

- Operating Temperature:
   -65°C to +200°C
- Electrical Resistance: Meets ≤1.0 mΩ requirement of AS85049/128
- Corrosion Resistance: 500 hr. salt spray

## Mechanical

- Tensile Strength: 200 lb.
- Braid Retention: Meets 100 lb. requirement of AS85049/128

#### **Application Tooling**

• Micro Tie-Dex II, A30199

Description	Part No.	
Bandstrap	BND-0812S	

#### **ACCESSORIES**

#### **Heat-Shrinkable Molded Boots**



#### **Hazard Matched**

- Different materials to meet different temperature and environmental requirements
- Optional with pre-applied adhesives for quick installation and high-reliability IP67 sealing
- Epoxy sealing kits available

#### Versatile

- Sealing and strain relief to the wires and cables
- Straight or 90 degree cable exit

#### **Application Tooling**

 HL1910E or the HG-501A ThermoGun heat gun and appropriate hot air reflectors

#### **Product Offering**

Temperature	Material	Adhesive Lined	Size* mm	Descriptive Part No.	
Range				Straight	90°
-20°C to 60°C —	Flexible polyolefin	Yes	24/10.4/5.6	202K121-4/42-0	222K121-4/42-0
	Flexible polyolefin	Yes	30/14.2/5.9	202K132-4/42-0	222K132-4/42-0
-55°C to 120°C	to 120°C Fluid-resistant elastomer		30/14.2/5.9	202K132-25/86-0	222K132-25/86-0
-55°C to 135°C	Flexible polyolefin	No	30/14.2/5.9	202K132-4-0	222K132-4-0
-55°C to 200°C	Modified fluoroelastomer	No	30/14.2/5.9	202K132-12-0	222K132-12-0
-75°C to 150°C —	Fluid-resistant elastomer	Yes	30/14.2/5.9	202K132-25/225-0	222K132-25/225-0
	Fluid-resistant elastomer	No	30/14.2/5.9	202K132-25-0	222K132-25-0

<sup>\*</sup>Size = as-supplied diameter both ends/recovered diameter connector end/recovered diameter cable end.

#### **High-Data-Rate Cables**



#### **Compact and Lightweight**

- Thin-wall technology for smaller, lighter cables
- 28 AWG to 22 AWG conductors

#### **Versions for Common Protocols**

- Fast and Gigabit Ethernet in Cat 5e and Quadrax configurations
- IEEE 1394
- USB

#### Rugged

- Specialized TE developed polymer formulations designed to support better mechanical and thermal performance in harsh environments
- State-of-the-art FAA approved foam dielectrics for better signal transmission
- Ruggedized zero halogen jacket for marine applications that passes the rigorous military standards for flammability while meeting stringent smoke and toxicity requirements

#### Customizable

- Customizable to meet missioncritical needs such as EMI, fluid resistance, and flammability
- Hybrid designs
- Electrical testing capability, including skew and eye patterns

#### Robust

- Operating temperature range from -55°C to +200°C
- Full range of shielding options for signal integrity

# Empower Engineers to Solve Problems, Moving the World Forward.

AMP | AGASTAT | CII | DEUTSCH | DRI | HARTMAN | KILOVAC MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | SEACON

## **CONNECT WITH US**

We make it easy to connect with our experts and are ready to provide all the support you need. Visit **te.com/support** to chat with a Product Information Specialist.

#### **QUALITY STARTS WITH THE RIGHT APPLICATION TOOLING**

Creating a quality crimp connection is essential to delivering high performance and reliability in extreme environments. From low to high volume wire processing, TE has you covered with a full range of application tooling and a global field service team.

- · View all application tooling
- · Connect with our experts to find the right tool for your application

# te.com/highspeed

AMP, AGASTAT, CeeLok FAS-T, CII, DEUTSCH, DRI, HARTMAN, KILOVAC, MICRODOT, NANONICS, POLAMCO, Raychem, Rochester, SEACON, SolderSleeve, ThermoGun, TE, TE Connectivity, and TE connectivity (logo) are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity All Rights Reserved.

1-1773464-2 05/21

#### **CeeLok FAS-T CONNECTORS**

TE Connectivity Aerospace, Defense & Marine 2900 Fulling Mill Road Middletown, PA 17057

