



OAC Series

AC Output Modules

cas File E29244

Users should thoroughly review the technical data before selecting a product part number. It is recommended that users also seek out the pertinent approvals files of the agencies/laboratories and review them to ensure the product meets the requirements for a given application.

Features

- .6" (15.2mm) thick package.
- 4000V rms optical isolation.
- High immunity to false operation.
- · Series compatible.
- Output modules can be controlled from sinking or sourcing logic.
- Compatible with 2IOM series mounting boards.

Engineering Data

Switch Form: 1 Form A (SPST-NO)

Duty: Continuous.

Operating Temperature: -30°C to +80°C. Storage Temperature: -30°C to +100°C. Potting Compound Flammability: UL94V-0. Solderability: 260°C for 5 seconds, maximum.

Approximate Weight: 1.38 oz. (35g).

Ordering Information

Typical Part Number >

-5

OAC

A

- **1. Basic Series: OAC** = AC output module black case
- **2. Input Voltage:** 5 = 5VDC 15 = 15VDC 24 = 24VDC
- 3. Output: Blank = 3A, 12-120VAC, zero voltage turn-on output

 $A=3A,\,24-280VAC,\,zero$ voltage turn-on output $H=5A,\,24-280VAC,\,zero$ voltage turn-on output

R = 24-280VAC, Random Turn-On

Our authorized distributors are more likely to maintain the following items in stock for immediate delivery.

OAC-5 OAC-5H OAC-24 OAC-5A OAC-15 OAC-24A

Input Specifications

Parameter	Conditions	Units	OAC-5 OAC-5A OAC-5H OAC-5R			OAC-15 OAC-15A OAC-15H OAC-15R			OAC-24 OAC-24A OAC-24H OAC-24R		
			Min.	Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.
Control Voltage Range VIN		VDC	3	5	8	9	15	18	18	24	32
Must Operate Voltage VIN(OP) (Min.)		VDC			3			9			18
Must release Voltage VIN(REL) (Min.)		VDC	1			1			1		
Input Current	@VIN=Nominal	mADC	2 - 10			6 - 12			4 - 12		
Input Resistance RIN		Ohms				Current Regulator					

PIN-3 must be positive with respect to PIN-4 for correct operation.



OAC Series (Continued)


AC Output Modules


Output Specifications (47 to 63 Hz.,@+25°C unless otherwise specified)

Parameter	Conditions	onditions Units		OAC-5 OAC-15 OAC-24		OAC-5A OAC-15A OAC-24A			OAC-5H OAC-15H OAC-24H			OAC-5R OAC-15R OAC-24R		
			Min.	Тур.	Max	Min.	Тур.	Max	Min.	Тур.	Max.	Min.	Тур.	Max.
Load Voltage V∟		V rms	12		120	24		280	24		280	24		280
Repetitive Blocking Voltage		V peak			400			600			600			600
Load Current I∟*		A rms	.05		3	.05		3	.05		5	.05		5
Single Cycle Surge Current		A peak		208			208			300			300	
Leakage Current (Off-State)	VL=280VAC	mA rms			5			5			5			5
On-State Voltage Drop	IL=Max.	V rms			1.8			1.8			1.6			1.6
Static dv / dt (Off-State)		V/µs		475			475			300			300	
Turn-On Time	@f 00/50 LI-	ms		8.3 / 10			8.3 / 10			8.3 / 10			0.1	
Turn-Off Time	@f=60/50 Hz.	ms		8.3 / 10			8.3 / 10			.3 / 10			8.3	
HP / Rating	@ 240VAC	HP		1/4			1/4			1/2			1/2	


^{*} See Derating curve


OAC Operating Diagram






OAC Derating Diagram






Outline Dimensions



PCB Layout



Note : Extra nut and washer will be provided on the screw, which will goes under PCB to fix the relay. Hex Nut S= 6.35 (width across flats), Thickness = 2.40; Washer = OD : Φ 485 \pm 0.25, ID : Φ 2.75 \pm 0.15, Thickness : 0.55