





FEATURES

- O-Ring Mount
- -40°C to +125°C Operating Temperature
- Up to ±0.2% Pressure Non-Linearity
- Solid State Reliability

APPLICATIONS

- Medical Instruments
- Process Control
- Fresh & Waste Water Measurements
- Partial Vacuum Gas Measurement
- Pressure Transmitters
- Tank Level Systems (RV & Industrial)

STANDARD RANGES

Range	psi
0 to 15	•
0 to 30	•
0 to 50	•
0 to 100	•
0 to 300	•
0 to 500	•

154NVU

Vacuum Gage, Uncompensated

SPECIFICATIONS

- 316L SS Pressure Sensor
- 19mm Diameter
- Vacuum Gage

Model 154NVU is an uncompensated, micro-machined, piezoresistive silicon pressure sensor designed for vacuum gage applications, packaged in a 316L Stainless Steel housing.

This product features O-ring mounting and is designed for OEM applications where compatibility with corrosive media is required. The sensing package utilizes silicone oil to transfer pressure from the 316L Stainless Steel diaphragm to the sensing element.

For additional Model 154N products designed for vacuum gage applications, datasheets for Compensated and Constant Voltage configurations are available.



PERFORMANCE SPECIFICATIONS


PARAMETERS MIN TYP MAX Sensitivity 12 27 mV Zero Pressure Output -6.0 8.0	UNITS NOTES //V @Span 1 mV/V 1 %Span 2
·	mV/V 1
Zero Pressure Output -6.0 8.0	
2010 1 1000010 Cut.put	0/ Cnon
Pressure Non-Linearity -0.2 0.2	%Span 2
Pressure Hysteresis -0.05 0.05	%Span
Repeatability ±0.02	%Span
Bridge Resistance 3.8 5.8	$k\Omega$ 3
Thermal Hysteresis – Span -0.25 ±0.05 0.25	%Span 4
Thermal Hysteresis – Offset -0.25 ±0.05 0.25	%Span 4
Temperature Coefficient – Resistance 1.30 1.51 1.75 kg	(PPM/°C 4
Temperature Coefficient – Span -1.65 -1.25 -1.0 k	kPPM/°C 4
Temperature Coefficient – Offset -30 30	μV/V/°C 4
Long Term Stability – Span ±0.10 %S	Span/Year
Long Term Stability – Offset ±0.10 %S	Span/Year
Supply Current 0.5 1.5 2.0	mA
Supply Voltage 5 9.5	V
Output Noise (10Hz to 1kHz) 1.0	μV p-p
Response Time (10% to 90%) 0.1	ms
Insulation Resistance (50V _{DC}) 50	ΜΩ 5
Pressure Overload 3X	Rated 6
Pressure Burst 4X	Rated 7
Operating Temperature -40 +125	[©] C
Storage Temperature -50 +125	ºC
Media – Pressure Port Liquids and Gases compatible with 316/316L Stainless St	teel

Notes

- 1. Measured at Ambient Pressure.
- 2. Best fit straight line.
- 3. Bridge resistance is measured with both –E pins shorted together.
- 4. TC values are first order coefficients to a quadratic fit over a temperature range of -20 to +85°C.
- 5. Between case and sending element.
- 6. The maximum pressure that can be applied without changing the transducer's performance or accuracy.
- 7. The maximum pressure that can be applied to a transducer without rupture of either the sensing element or transducer.
- 8. Testing:
 - 8.1 Units are not tested over temperature or pressure
 - 8.2 A final electrical test (@ 1.5mA) is performed to verify parts are electrically alive.
 - 8.3 All units are subjected to 100% drift test.
- 9 Marking:
 - Each part is identified with Model Number, Pressure Range, Type, Lot Number, Serial Number and Date Code
- 10 Shipping/Packaging:
 - The diaphragm is protected by static dissipative cap. Each is packaged individually in a plastic vial with anti-static foam.
- 11 Direct mechanical contact with diaphragm is prohibited. Diaphragm surface must remain free of defects (scratches, punctures, dents, fingerprints, etc) for device to operate properly. Caution is advised when handling parts with exposed diaphragms. Use protective cap whenever devices are not in use.




DIMENSIONS




SENSO	R PINOUT
PIN NO	FUNCTION
1	-OUT
2	-EX2
3	+OUT
4	+EX
.5	-EX1



CONNECTIONS



ORDERING INFORMATION



NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: +1 800-522-6752

Email: customercare.frmt@te.com

EUROPE

Measurement Specialties (Europe), Ltd., a TE Connectivity Company Tel: +31 73 624 6999

Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: +86 0400-820-6015

Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved