



## HDC- HK- HDW3/1/1-23/16/47

TE Connectivity's Heavy Duty Connectors (HDC) deliver outstanding, reliable performance in harsh environments. Designed specifically for high performance EMV demand for industrial applications, the new HDC HK-HDW3/1/1-23/16/47 combines power and signal in one small H10B hood with EMC shielding. The connector has a high density involving 47 positions of signal (2.2A 32V), 16 positions of power (3.7 A 300V) and 23 positions of power (11A 400V). The Dynamic contact makes it possible to reduce cable assembly costs by using semi-automatic or fully-automatic crimping of dynamic contacts. Building on TE's proven Dynamic contacts technology, the new HDC HK insert deliver performance comparable with traditional HDC connectors.

### BENEFITS

- Use one connector instead of two for signal and power transmission
- Save space as EMC shielding is integrated in the hybrid solution
- Box shaped contacts enables high density modular system in HDC connector
- One contact family for wire-to-board, wire-to-wire and heavy-duty cable-to-cable connections
- Designed for harsh (industrial) environments as the connector is suitable for IP65 and IP68 / IP69K protection

### FEATURE

- **Hybrid Power+Signal**
  - Signal (HD1) 47P (2.2A 32V)
  - Power (HD1) 16P (3.7 A 300V)
  - Power (HD3) 23P (11A 400V)
- **Reliable and high density**
  - Signal (HD1) 47P (2.2A 32V)
  - Power (HD1) 16P (3.7 A 300V)
  - Power (HD3) 23P (11A 400V)
- EMC Shielding
- Reliable dynamic stamping contact

### STANDARD

- **EN 61984:** Connectors - Safety requirements and tests
- **IEC 60068:** Environmental testing
- **IEC 60512:** Connectors for electronic equipment - Test and measurements
- **IEC 60529:** Degrees of protection provided by enclosures (IP Code)
- **IEC 60664-1:** Insulation coordination for equipment within low-voltage systems (Part 1)
- **EN 61373:** Railway application - Rolling stock equipment - Shock and vibration test
- **ISO 6988:** Metallic and other non-organic coatings - Sulfur dioxide test with general condensation of moisture

### APPLICATIONS

- Industrial robot
- Cobot
- Scala robot
- Controller
- Machinery

### ELECTRICAL

- 2.2A/32V
- 3.7A/300V
- 11A/400V

### MECHANICAL

- Housing locking strength
- 100 N Min

### MATERIALS

- PBT GF

### SPECIFICATIONS

- 108-137458

PART NUMBER LIST

Type	Part Number	Part Description
Male Insert	T2120865101-000	HK-HDW3/1/1-23/16/47-M
Female Insert	T2120865201-000	HK-HDW3/1/1-23/16/47-F
Shielding plate Option 1, Male insert in hood side	T0920013670-000	M SHIELD PLATE FOR HK-HDW3/1/1, BENDED
	T0920023670-000	F SHIELD PLATE FOR HK-HDW3/1/1, STRAIGHT
Shielding plate Option 2, Female insert in hood side	T0920013670-001	M SHIELD PLATE FOR HK-HDW3/1/1, STRAIGHT
	T0920023670-002	F SHIELD PLATE FOR HK-HDW3/1/1, BENDED
Hood with 2 holes	T1220102025-000	H10B-TG-M20/M25, SHORT RIB
Hood with 1 top entry hole	T1240100132-002	H10B-TGH-M32, SHORT RIB
Hood with 1 side entry hole	T1230100132-002	H10B-TSH-M32, SHORT RIB
Housing	T1410100000-001	H10B-AG-SL, ONE RIB

**Note:**

- \* Depends on insert installation type to selective one option of shielding plate
- \* Depend on cable type to select one type of hood.

Series Items	Contact Size (Insulation range (mm))	Applicable Contact	
		Tab	Receptacle
		Part Number	Part Number
HK-HDW3/1/1-23/16/47- M/F POWER (23 POS)	S (0.8-1.4)	2316815-1: Reel 2316817-1: L/P	2298107-1: Reel 2311162-1: L/P
	M (1.2-2.6)	2316815-2: Reel 2316817-2: L/P	2298107-2: Reel 2311162-2: L/P
	L (1.8-2.8)	2316815-3: Reel 2316817-3: L/P	2298107-4: Reel 2311162-4: L/P
	2L (2.2-2.8)	2316815-4: Reel 2316817-4: L/P	2316815-5: Reel 2298107-5: Reel
	3L (3.1-3.4)	2316815-5: Reel	2298107-5: Reel
	3L (3.1-3.8)	2316817-5: L/P	2311162-5: L/P
HK-HDW3/1/1-23/16/47- M/F POWER (16 POS)	S (0.6-1.2)	2316663-1: Reel 2316669-1: L/P	2316670-1: Reel 2316671-1: L/P
	M (1.08-1.6)	2316663-2: Reel 2316669-2: L/P	2316670-2: Reel 2316671-2: L/P
	L (1.08-1.9)	2316663-3: Reel 2316669-3: L/P	2316670-3: Reel 2316671-3: L/P
	2L (1.4-2.2)	2316663-4: Reel 2316669-4: L/P	2316670-4: Reel 2316671-4: L/P
HK-HDW3/1/1-23/16/47- M/F SIGNAL (47 POS)	S (0.6-1.2)	2316663-1: Reel 2316669-1 : L/P	2316670-1: Reel 2316671-1: L/P
	M (1.08-1.6)	2316663-2: Reel 2316669-2: L/P	2316670-2: Reel 2316671-2: L/P

te.com

© 2020 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773985-1 01/21 AK