

# Type CP16 Series

#### **Key Features**

- High Reliability
- Small Versatile Size
- All Plastic Body
- Plastic or Metal shaft styles
- Switch Types Available
- Multiple Sections Available
- Flatted, Serrated Shaft Available



Specify the type CP16 for applications where high subton resistance and voltage proof are key requirements. The materials used in the all-purstic bridy and spindle construction make it an ideal component for domestic applinaces and control systems where safety is of prime importance. This popular low cost potentiometer is suitable for industrial and professional applications.

### Characteristics - Electrical

Resistance Range:	20R to 4MZ Linear, 2K2 to 2M2 Non-Linear		
Resistance Values:	1, 2, 8, 7 in each decade		
Resistance Tolerance:	20% (>1M ± 30%) - ±10% by selection		
Power Rating @ 40°C:	2 Watts Linear - 0.1 Watts Non-Linear		
Limiting Element voltage.	250 Volts dc (Linear), 125 Volts dc (Non Linear)		
Electrical Relation:	260° ± 20°		
Terminal Resistance:	5 ohms, maximum ⊴0.1% (2 ohms, minimum)		
Nois EN:	≤3% (3 ohms minimum)		
Instation less ance:	4G ohms, minimum		
Reson on:	Essentially Infinite		
Vol. ge F. V.	1KV ac peak		

# 

End Torque:	400 mNm maximum	
Operating Torque:	5 to 25 mNm maximum	
Mechanical Adjustment:	300° ± 5°	
Maximum Torque to Nut:	800 mNm	

#### **Characteristics - Environmental**

Electrical Life:	ΔR± 5% (1000 hours 0.2 Watts @ 40°C)	
Mechanical Life:	25,000 operations	
Operating Temperature:	-25°C to +70°C	
Temperature Coefficient:	± 300ppm/°C (Rn <100K ohms)	
Thermal Cycling:	ΔR± 2.5% (16 hours 85°C, 2 hours @ -25°C)	
Damp Heat:	ΔR± 5% (500 hours @ 40°C +95% RH)	
Vibration:	ΔR± 2% (2 hours @ 20g - 10Hz ~50 Hz)	

## 1773199 Rev. C 07/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change


For Email, phone or live chat, go to: www.te.com/help



# **Type CP16 Series**

## Switch Specifications

Nominal Current:	1A, 250 VAC	
Contact Resistance:	10 milli ohms	
Operating Torque:	10 to 30mNm	
Operating Angle:	30° ± 5°	
Test Voltage:	500 V	




1773199 Rev. C 07/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change

For Email, phone or live chat, go to: www.te.com/help





Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change

For Email, phone or live chat, go to: www.te.com/help