

600 series **15 Amp Sensitive** PC Board Relay

A File E55708 (File LR48569

Users should thoroughly review the technical data before selecting a product part number. It is recommended that users also seek out the pertinent approvals files of the agencies/laboratories and review them to ensure the product meets the requirements for a given application.

Features

- Low power sensitive coil.
- 1 Form A, 1 Form B and 1 Form C contact arrangements.
- Various contact materials and types for ratings to 15 amps.
 Coil assembly rated 130°C, 94V-O.
- Applications include sensor and timer controls, emergency lighting, instrmentation, alarm systems, smoke and fire detectors, business equipment and vending machines.

Contact Data

Arrangements: 1 Form A (SPST-NO), 1 Form B (SPST-NC) and 1 Form C (SPDT)

Material and Type: Gold-silver crossbar, silver-cadmium crossbar, palladium crossbar, gold-flashed silver cadmium, silver sadmium oxide, find silver, gold-flashed coin silver.

Expected Mechanical Life: 10 million operations, minimum. Expected Electrical Life: 100,000 operations, minimum, at rated load.

UL/CSA Ratings @ 25°C

/CSA Ratings @ 25°C de Contact Material Rating							
Contact Material	Rating						
Au Flashed AgCd	75VA@24VAC Pilot Duty§ 1A@120VAC General Purpose 1.5A@50VDC Resistive 600W@277VAC Gen'I. Purpose SPST-NO Only 240W@277VAC Gen'I. Purpose SPST-NC Only 480VA@277VAC Pilot Duty SPDT Only 480VA@Ballast SPDT Only 1/10 HP@120VAC						
Au Ag	3A@28VDC Resistive 125VA@120VAC Pilot Duty§ 1/8 HP@120/240 VAC						
AgCdO	15A@150VAC Inductive 0.4 PF NO Only 10A@277VAC Resistive 15A@28VDC Resistive TV5@NO Contacts TV2@NC Contacts 600W@277VAC Tungsten SPDT-NO Only 240W@277VAC Tungsten SPDT-NC Only 480VA@277VAC Pilot Duty SPDT Only 480VA@277VAC Ballast SPDT Only 1/3 HP@120/240VAC NO 1/6 HP@120/240VAC NC						
Au Flashed Coin Ag	5A@240VAC Resistive 5A@28VDC 125VA@240VAC Pilot Duty § 125VA@125VAC Pilot Duty §						
Fine Ag	15A@150VAC Resistive 15A@28VDC Resistive 10A@277VAC Resistive 480VA@240VAC Pilot Duty TV2@NC Contacts TV4@NO Contacts 480W@120VAC Tungsten NO 240W@120VAC Tungsten NC						
Ag Cd	3A@240VAC Resistive 3A@28VDC Resistive						
Palladium	2A@28VDC Resistive						
	Contact Material Au Flashed AgCd Au Ag AgCdO Au Flashed Coin Ag Fine Ag Ag Cd						

§ Only when Code Y Electrical Spacing is specified.

Dimensions are shown for reference purposes only.

Dimensions are in inches over (millimeters) unless otherwise specified.

Initial Dielectric Strength

Between Open Contacts: 500VAC, 60 Hz., 2 seconds. Between Coil and Contacts: 1,000VAC, 60 Hz., 2 seconds.

Coil Data @ 25°C

Rated Voltage: 3 to 48VDC. Maximum Voltage @ 85°C: 120% of Rated Voltage. Nominal Power @ 25°C: 110mW for 3A and 5A rated models; 240mW for 15A rated models.

Maximum Power @ 25°C: 1W.

Duty Cycle: Continuous. Initial Insulation Resistance: 10,000 megohms, min., at 25°C, 500VDC and 50% rel. humidity.

Coil Data @ 25°C

Nominal Voltage	DC Resistan ±10	Must Operate Voltage	Must Release Voltage		
VDC	3 A & 5A Types	15A Types	VDC	VDC	
3	82	38	2.25	0.3	
6	327	150	4.5	0.6	
9	736	338	6.75	0.9	
12	1,309	600	9.0	1.2	
18	2,945	1,350	13.5	1.8	
24	5,236	2,400	18.0	2.4	
28	7,127	3,267	21.0	2.8	
48	20,945	9,600	36.0	4.8	

Operate Data @ 25°C

Must Operate Voltage: 75% of nominal. Must Release Voltage: 10% of nominal. Operate Time: 10 ms, typ. Release Time: 10 ms, typ.

Environmental Data

Temperature Range: Storage: -55°C to +85°C. Operating: -55°C to +85°C.

Mechanical Data


Termination: Printed circuit terminals. Enclosures: Unsealed dust cover or sealed plastic case. Weight: 1.6 oz. (45g) approximately.

Specifications and availability subject to change.


RELAY PRODUCTS	Catalog 1308242 Issued 3-03 (PDF Revised 9-12)						P&B
1. Basic Series Type:			3	- 24	v	Y	Q
60 = Miniature, PC board relay rated 3A or 5A (Contact Material Code G, S, V or B only) 61 = Miniature, PC board relay rated 15A (Contact Material Code H or R only) 65 = Miniature, PC board relay rated 5A (Contact Material Code K only) 2. Contact Arrangement:							
1 = 1 Form A (SPST-NO) 2 = 1 Form B (SPS 3. Coil Voltage: 3 = 3VDC 9 = 9VDC 18 = 18VDC 6 = 6VDC 12 = 12VDC 24 = 24VDC	ST-NC) 3 = 1 Form C (28 = 28VDC 48 = 48VDC	(SPDT)					
6 = 6VDC 12 = 12VDC 24 = 24VDC 48 = 48VDC 4. Contact Material: G = Au Ag crossbar, rated 3A (Only available with Basic Series Type 60). S = Au Cd crossbar, rated 3A (Only available with Basic Series Type 60). V = Pd crossbar, rated 3A (Only available with Basic Series Type 60). B = Au-flashed AgCd crossbar, rated 5A (Only available with Basic Series Type 60). H = AgCdO, rated 15A (Only available with Basic Series Type 61). R = Fine Ag, rated 15A (Only available with Basic Series Type 61). K = Au-flashed coin Ag, rated 5A (Only available with Basic Series Type 65).							
5. Electrical Spacing: Leave Blank = 0.125 in (3.175 mm) Clearance and 0.125 in (3.175 mm) Creepage Y = 0.125 in (3.175 mm) Clearance and 0.250 in (6.35 mm) Creepage							
6. Enclosure Type Leave Blank = Unsealed dust cover	Q = Sealed cover						

Our authorized distributors are more likely to stock the following items for immediate delivery. None at present.

Outline Dimensions



PC Board Layout (Bottom View)



Note: On single throw models, only necessary terminals are present.

Disclaimer

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current.

TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose.

The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2012 Tyco Electronics Corporation


a TE Connectivity Ltd. company

TE Connectivity (logo) and TE Connectivity are trademarks of the TE Connectivity group of companies and its licensors.

Other logos, product or company names may be trademarks of their respective owners.

Dimensions are in inches over (millimeters) unless otherwise specified.

Wiring Diagrams (Bottom Views)



Note: On single throw models, only necessary terminals are present.