

### Type ME Series

# PRODUCT PLANNED FOR EOL LTB 18/08/23

### Type ME Series



Tyco Electronics is a feading supplier of standard and customdesigned vitreous enamel power resistors for industrial, control, and general-purpose applications.

The ME Range of wire and tape wound tubular resistors is designed for maximum power density (in free air), and a durable vitreous ename! coating provides a reliable and resilient, high power solution.

Resistors are supplied with flexible wire terminations or tags (for screw, solder or "Faston" connection). Options include low inductance winding, different tube sizes for a given power rating, and a range of mechanical packages including horizontal or vertical mounting.

Tyco Electronics is happy to advise on the use of resistors for pulse applications and to supply information for high voltage use, low-ohmic values, alternative mountings and termination types in addition to fasting resistors to conform to relevant international, MIL or customer specifications.

#### **Key Features**

- High Power Dissipation in
  - . No need for a heatsink
- Overload 15 Times Rated Power
  - A compact and cost effective solution
- Mechanically Stable in
  Demanding Environments
  Vitreous Enamel coating
  resists impact and
  temperatures of 400°C
- Broad Range of Options: Adjustable Resistance, Low TCR, Custom Design Capability
  - Gives ultimate design flexibility
- Established Product with Proven Reliability
  - Consistent high quality at a competitive price
- 48 Standard Products from 30W to 625W
- The solution for your application

#### Characteristics -Electrical

	Power Reference - Power at 360°C (W)									
	30		4	0	45			50		
Type:	Power at 380°C	R Values	Power at 380°C	R Values	Power at 380°C	R Values	Power at 380°C	R Values		
E (Standard):	35W	2R2-5K0	65W	4R7-10K	65	4R7-10K	70W	4R7-10K		
MA ( Adjustable):					12	-				
MF (Ferrule Ends): MD (Ferrule Dead End):					65	4R7-10K				
MT (Tape Wound):	44W	R02-2R0	80W	R15-4R5	80W	R20-4R5	90W	R20-4R5		

	Power Reference - Power at 360°C (W)										
		0	13	10	150		-1	80			
Туре:	Power at 380°C	R Values	Power at 380°C	R Values	Power at 380°C	R Values	Power at 380°C	R Values			
ME (Standard): MA ( Adjustable): MF (Ferrule Ends): MD (Ferrule Dead End):	125W	10R-22K	175W	10R-22K	=185W	12R-22K	230W	22R-22K			
MT (Tape Wound):	185W	R30-9R0	215W	R70-9R0	245W	R80-10R	285W	1R0-20R			


	Power Reference - Power at 360°C (W)									
	2	20	32	20	380					
Туре:	Power at 380°C	R Values	Power at 380°C	R Values	Power at 380°C	R Values				
ME (Standard): MA ( Adjustable):	320W	22R-22K	450W	33R-22K	500W	47R-22K				
MF (Ferrule Ends): MD (Ferrule Dead End):	1B		Ø3	Œ	120	:35				
MT (Tape Wound):	400W	1R0-20R	560W	1R5-30R	625W	1R5-30R				

Damp Heat:	56 days 90 - 95% ΔR < ± 2%
Storage Temperature:	-55°C to +200°C
Tolerance:	±5% ±10%
The state of the s	THE PARTY AND TH

## Applications

- Braking
- Crowbar
- In-rush Limiting
- Balancing
- Capacitor Charging & Discharging
- Filter
- Electrical Machinery

### Dimensions - MF & MD Type





	MF & MD Type										
	30	40	45	60L	608	90L	908	130	180	220	
S	76	127	83	121	102	197	133	184	248	298	
T	65	116	70	108	90	184	121	171	235	286	
U	14	14	27	21	27	21	27	27	27	27	
٧	19	19	32	22	32	22	32	32	32	32	
W	4BA	4BA	OBA	2BA	OBA	2BA	OBA	OBA	0BA	OBA	
										_	

te.com 1773247 Rev. B 05/2023



### Dimensions - ME, MA & MT\* Type






	ME, MA & MT* Type												
	30	40	45	60L	608	90L	908	130	150	180	220	320	380
Α	51	102	51	89	70	165	102	152	178	216	2667	267	305
B*	19	19	32	32	32	22	32	32	32	32	32	45	45
C	9.5	9.5	19	12.6	19	12.6	19	19	19	19	19	28	28
D	25	25	37	30	37	30	37	37	37	37	37	43	43
E	6.3	6.3	6.3	6.3	6.3	6.3	9.5	9.5	9.5	9.5	9.5	9.5	9.5
F	4BA	48A	48A	4BA	4BA	48A	2BA	2BA	28A	2BA	2BA	2BA	28/
G	72	123	91	117	110	193	142	192	218	256	307	318	356
H	62	113	75	103	94	179	126	176	202	240	291	291	327
HR	42	93	30	77	48	153	80	130	156	194	245	248	286
J	16	16	28	20	28	20	28	28	28	28	28	44	44
K	20	20	27	27	27	27	27	27	27	27	27	51	51
L	64	114	64	102	83	178	114	165	119	229	279	- 12	140
M	38	38	54	45	54	45	54	54	54	54	54	134	
N	25	25	41	32	41	32	41	41	41	41	41	- 6	-
P	4 x 6	4 x 6	5 x 8	4 x 6	5 x 8	4 x 6	5 x 8	5 x 8	5 x 8	5 x 8	5 x 8	26	*
R	4 x 6	4 x 6	5 x 13	5 x 8	5 x 13	5 x 8	5 x 13	18	30				

<sup>\*</sup> For MT type, dimension B may increase by up to 10mm due to tape width.


### **Derating Curve**




te.com 1773247 Rev. B 05/2023



#### Power Overload



### Surface Temperature Rise in Free Air





While TE has made every reasonable effort to ensure the accuracy of the information in this Data Sheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

te.com 1773247 Rev. B 05/2023