

Direct Power Connection for Bus Bars





#### Introduction

#### **Features and Benefits**

#### **Current:**

150 A

#### **Mating Force:**

40 N max.

# Mating Bus Bar Thickness:

 $3.0 \pm 0.1 \text{ mm}$ 

#### **Bus Bar Misalignment:**

±0.75 mm max.


#### Hot Pluggable:

Yes

#### **Contact Resistance:**

0.2 milliohms max.

- Blind Mate
- Anti Over Stress Feature
- Reduced Installation Costs
- Screw Fix or PC Tail Option



# **Technical Features**

**Product Specification:** 108-19360

**Application Specification:** 114-19128

The CROWN CLIP JUNIOR connector provides a space efficient connector in solder or screw mount configurations ideal for power supply/distribution applications. Satisfying the demand for low insertion/extraction forces it is hot plug capable for controlled and reliable separation of high power.


The connector mates to a 3.0 mm thick plated Bus Bar that provides a separable interface to ease assembly, inspection and trouble shooting.

The selective plated, high conductivity copper contacts offer low resistance and low millivolt drop for efficient power distribution. In blind mate applications this connector can handle adverse tolerances through the unique antistress feature allowing reliable mating to misaligned bus bars.

The CROWN CLIP JUNIOR connector can be soldered direct to a PCB or screwed to a Bus Bar for a 150 A maximum current capacity.

# **Applications**

- Core Network Energy Systems
- Cellular Base Stations
- PSU Power Distribution
- Servers, Storage & Network Routers
- Industrial



Direct Power Connection for Bus Bars

www.tycoelectronics.com

# Screw Mount

# **Materials and Plating**

# **Bus Bar**

**Conductor:** 

Copper

Plating:

Nickel or suitable alternative

Temperature:

-40 °C to +125 °C

#### Connector

### **Conductor:**

High Conductivity Copper Alloy

### Plating:


Nickel or suitable alternative

# Insulator:


Thermoplastic, glass reinforced

#### Temperature:

-40 °C to +125 °C



Part No. 1982995-1



# **PCB Mount**

# **Materials and Plating**

### **Bus Bar**

**Conductor:** 

Copper

Plating:

Nickel or suitable alternative

Temperature: -40 °C to +125 °C

#### Connector

### Conductor:

High Conductivity Copper Alloy

### Plating:


Nickel or suitable alternative

# Insulator:


Thermoplastic, glass reinforced

#### Temperature:

-40 °C to +125 °C



Part No. 1982530-1



Direct Power Connection for Bus Bars

Catalog 1654261-8 Issued 9-2008 www.tycoelectronics.com

# Technical Data

### Performance and Test Description

The product is designed to meet electrical, mechanical and environmental performance specified in Design Objectives 108-19360.

Unless otherwise specified, all tests are performed at ambient environmental conditions per IEC specification 60068-1 clause 5.3 and are performed with connectors in mated condition.

#### **Visual**

Para- graph	Test Title	Performance / Severity Requirements	Procedure
1.1.1	Examination of product	Meets requirements of product drawing and applicable instructions on customer drawing, and application specification.	Visual, dimensional and functional per applicable inspection plan. In acc. with IEC 60512-1-1 Magnification 10x

# **Electrical**

Licotrical				
1.1.2	Contact resistance	0.2 milliohms max.	Subject contacts assembled in housing and mated to a bus bar conductor to 50 mV maximum open circuit at 100 mA DC maximum.	
1.1.3	Insulation resistance	5000 M $\Omega$ min. initial (After moisture 1000 M $\Omega$ min.)	Test voltage 500 V DC, duration 1 minute. In acc. with IEC 60512-3-1	
1.1.4	Voltage proof	Requirement: no break-down or flash-over.	Test voltage: 1000 V AC Duration 1 minute. In acc. with IEC 60512-4-1 Test between 2 connectors when mounted on a PCB with a pitch of 25 ± 1 mm.	
1.1.5	Hot insertion/extraction	Contact resistance after test 0.2 milliohms maximum.	Min. 10 mating/unmating cycles. Mating/unmating speed between max. 750 mm/s and min. 50 mm/s. Current: 150 A	



# Direct Power Connection for Bus Bars

Issued 9-2008 www.tycoelectronics.com

# Technical Data

#### **Mechanical**

Para- graph	Test Title	Performance / Severity Requirements	Procedure
1.1.6	Mating force	20 N maximum	Measure force necessary to mate samples with a Bus Bar conductor.
1.1.7	Unmating force	5 N minimum	Measure force necessary to unmate samples with a Bus Bar conductor.
1.1.8	Durability	No damage allowed.	With connector mounted on PCB mate and unmate samples for 50 cycles with a Bus Bar conductor.
1.1.9	Solderability	5 % maximum de-wetting.	Solder bath temperature 260 °C

# **Environmental**

1.1.10	Temperature cycling	-55 °C / 105 °C, 0.5 hrs / 0.5 hrs, Transition time: <2 sec. Number of cycles: 25 (unmated) Recovery time: 1 hour.	In accordance with IEC 60512-11-4
1.1.11	Damp/heat cyclic	25 °C/55 °C 12 hrs/12 hrs (= 1 cycle) RH 95 % Number of cycles: 10 (unmated)	In accordance with IEC 60512-11-12

**Direct Power Connection for Bus Bars** 

Sample Kit


# CROWN CLIP JUNIOR – Demo Kits

**Demo Kit Complete:** Part No. **2042631-1** 

Demo Kit – Slide only: Part No. 2042632-1

The CROWN CLIP JUNIOR connector display model is manufactured from clear acrylic which allows you see right to the heart of the connector function. The compact display model interactively demonstrates the connector features, ease of configuration and space efficient design of the CROWN CLIP JUNIOR connector.

This sample kit is available to order using part number specified above.



# Disclaimer

While Tyco Electronics Corporation and its affiliates referenced herein ("Tyco Electronics") have made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current.

Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. Tyco Electronics' only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale, and in no case will Tyco Electronics be responsible for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products. Users should independently evaluate the suitability of, and test each product for, their application.

The dimensions, specifications, designs, construction, materials and processes in this catalog are for reference purposes only and are subject to change without notice. Please consult Tyco Electronics for the most current product information.

The export of certain Tyco Electronics products is restricted by the Arms Export Control Act (Title 22, U.S.C. Sec 2751, et seq.) or the Export Administration Act of 1979, as amended (Title 50, U.S.C., App. 2401 et seq.). Orders may be subject to export approval by the U.S. Government. Buyer must comply with all applicable export laws of all applicable jurisdictions.

Tyco Electronics AMP GmbH AMPèrestr. 12-14 64625 Bensheim / Germany Phone: +49-(0)6251-133-0 Fax: +49-(0)6251-133-1600

www.tycoelectronics.com CROWN CLIP JUNIOR, TE Logo and Tyco Electronics are trademarks.

© 2008 Tyco Electronics Ltd. 1654261-8 Issued 9-2008 1.5M ST