

Type 3625 Series

Type 3625 Series



The 3625 series is used in similar applications to the 3624 series, however with a slightly different design aimed at very low resistence to keep power loss to a minimum. The 3625 series combines all the attributes of Tyco Sigma inductors to give an economically priced, high reliability product suited to power line DC-DC conversion applications and use within a wide range of electronic equipment applications.

Key Features

- Isat to 8A
- Irms to 7.2A
- Taped and Reeled
- Low RDC
- Available in 3 different sizes

PRODUCT PLANNED FOR EOL

LTB 18/08/2023

Electrical Characteristics -3625A Series

Inductance Code	Inductance (pH)	Tolerance	Test Freq. (Hz)	R.D.C. (Ω) Max.	Irms (A)	Isat (A)
1R5	1.5	±20%	100K	0.028	4.00	3.50
2R2	2.2	±20%	100K	0.030	3.30	2.80
3R3	3.3	±20%	100K	0.058	2.50	2.30
4R7	4.7	±20%	100K	0.065	2.20	2.00
6R8	6.8	±20%	100K	0.085	2.00	1.70
100	10.0	±20%	100K	0.115	1.70	1.50
150	15.0	±20%	100K	0.160	1.40	1.15
220	22.0	±20%	100K	0.210	1.25	0.95
330	33.0	±20%	100K	0.320	1.00	0.80
470	47.0	±10%	100K	0.450	0.75	0.70
680	68.0	±10%	100K	0.650	0.65	0.60
101	100.0	±10%	100K	0.880	0.52	0.50
151	150.0	±10%	100K	1.280	0.40	0.38
221	220.0	±10%	100K	1.920	0.33	0.30
331	330.0	±10%	100K	2.850	0.28	0.26
471	470.0	±10%	100K	4.350	0.22	0.21
681	680.0	±10%	100K	6.500	0.18	0.18
102	1000.0	±10%	100K	12.500	0.13	0.14

Electrical Characteristics - 3625B Series

Inductance	L	Tolerance Q Test Freq. (MHz) R.D.C. Irms			Irms	Isat		
Code	(µH)	toterance	Ref.	See Locate	0	(Ω) Max.	(A)	(A)
2R7	2.7	±20%	25	100K/0.1V	7.96	0.026	4.80	6.20
4R5	4.5	±20%	25	100K/0.1V	7.96	0.033	4.20	5.20
6R8	6.8	±20%	22	100K/0.1V	7.96	0.040	3.50	4.20
100	10.0	±20%	26	100K/0.1V	2.52	0.050	3.20	3.60
150	15.0	±20%	26	100K/0.1V	2.52	0.068	2.50	3.00
220	22.0	±20%	22	100K/0.1V	2.52	0.088	2.20	2.60
330	33.0	±20%	20	100K/0.1V	2.52	0.110	1.90	2.10
470	47.0	±20%	21	100K/0.1V	2.52	0.165	1.60	1,85
680	68.0	±20%	21	100K/0.1V	2.52	0.225	1.30	1.50
101	100.0	±10%	14	100K/0.1V	0.796	0.300	1.10	1.30
151	150.0	±10%	16	100K/0.1V	0.796	0.500	0.85	1.05
221	220.0	±10%	15	100K/0.1V	0.796	0.680	0.72	0.85
331	330.0	±10%	12	100K/0.1V	0.796	0.950	0.62	0.70
471	470.0	±10%	12	100K/0.1V	0.796	1,280	0.52	0.58
681	680.0	±10%	13.	100K/0.1V	0.796	1.920	0.43	0.46
102	1000.0	±10%	25	100K/0.1V	0.252	2.700	0.38	0.40

Electrical Characteristics -3625C Series

Inductance L		Totalina	Q	Test F	req.	S.R.F.	R.D.C.	Irms	Isat
Code	(µH)	Tolerance	Ref	L (Hz)	Q (MHz)	(MHz) Typ.	(m\(\Omega\)) Max.	(A)	(A)
2R5	2.5	±25%	20	100K/10mV	7.96	61.0	14	7.20	8.00
3R5	3.5	±25%	18	100K/10mV	7.96	43.0	16	6.00	7.00
4R6	4.6	±25%	20	100K/10mV	7.96	35.0	18	5.20	6.00
6R8	6.8	±25%	18	100K/10mV	7.96	32.0	24	4.30	5.20
100	10.0	±20%	25	100K/10mV	2.52	27.0	37	3.60	4.40
150	15.0	±20%	25	100K/10mV	2.52	24.0	46	3.30	3.70
220	22.0	±20%	26	100K/10mV	2.52	20.0	62	2.90	3.00
330	33.0	±20%	22	100K/10mV	2.52	16.0	85	2.50	2.60
470	47.0	±20%	20	100K/10mV	2.52	13.0	130	1.90	2.00
680	68.0	±20%	20	100K/10mV	2.52	11.0	165	1.65	1.80
101	100.0	±10%	18	100K/10mV	0.796	11.0	255	1.40	1.40
151	150.0	±10%	15	100K/10mV	0.796	8.0	380	1.20	1.15
221	220.0	±10%	15	100K/10mV	0.796	7.0	500	1.00	0.95
331	330.0	±10%	10	100K/10mV	0.796	6.0	700	0.85	0.80
471	470.0	±10%	10	100K/10mV	0.796	4.0	1150	0.67	0.70
681	680.0	±10%	10	100K/10mV	0.796	3.5	1400	0.60	0.58
102	1000.0	±10%	32	100K/10mV	0.252	2.7	2350	0.46	0.47




Type 3625 Series

Environmental Characteristics -


-40°C to +125°C
-40°C to +125°C (Temp. Rise included)
Base on Temp. Rise & AL/L = 10% Max.
40°C Max.

Dimensions



Series	A	В	C	D	E	E	G	H		J
3625A	6.0±0.3	6.0±0.3	2.8±0.5	2.0±0.3	1.9 typ.	2.2 ref.	2.4 ref.	6.7 ref.	2.3 ref.	2.1 ref.
3625B	10.0±0.3	10.0±0.3	4.5±0.3	2.4 typ.	2.0 typ.	6.0 ref.	2.8 ref.	10.4 ret.	2.4 ref.	5.6 ref.
3625C	12.7±0.3	12.7±0.3	4.80.3	3.0 typ.	2.0 typ.	8.6 ref.	3.6 ref.	13.6 ret.	2.6 ref.	8,4 ref.


Inductance Vs DC Superposition Characteristics - 3625A Series






Type 3625 Series

Inductance Vs DC Superposition Characteristics - 3625B Series



Inductance Vs DC Superposition Characteristics - 3625C Series



Reliability Test

Test Item	Specification	Test Condition
Thermal Shock Test: (Temp Cycle)	ΔL ≤ 10%	Room Temp. > -25± 2°C 15 minutes - > 30 minutes
		Room Temp > 85± 2°C 15 minutes > 30 minutes
		Total: 50 cycles
Humidity Resistance Test:	ΔL ≤ 10%	Temperature: 40± 2°C Humidity: 90 - 95% Applied Current: Per spec. Time: 500 hours
ligh Temp. Resistance Test:	ΔL ≤ 10%	Temperature: 85± 2°C Applied Current: Per spec. Time: 500 hours



Type 3625 Series



While TE has made every reasonable effort to ensure the accuracy of the information in this Data Sheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.