

### **Key Features**

- Available in 2 different packages
- Isat to 35A
- Irms to 38A
- Iron Core technology
- Low RDC
- Less than 6mm high
- Taped and Reeled





The 3635 series utilises state of the art fine magnet wire construction giving super low resistance and very, very high current ratings. Aligned with Tyco Sigma, reliability, quality and attractive costs makes the 3635 series an attractive product for a wide range of industrial applications where current capability is a key factor.

### **Electrical Characteristics - 3635A Series**

| Inductance<br>Code | Inductance  | Tolerance | Isat | Irms | R.D.C           | . (mΩ) |
|--------------------|---|-----------|------|------|-----------------|--------|
|                    | L (µH)  | Tolerance | (A)  | (A)  | Max.            | Тур.   |
| R70                | 0.70  | ±25%      | 15.0 | 16.0 | 4.8             | 3.7    |
| 1R0                | 1.00  | ±25%      | 12.0 | 13.0 | 6.0             | 4.6    |
| 1R5                | 1.50  | ±25%      | 10.0 | 11.0 | 6.9             | 5.3    |
| 2R0                | 2.00  | ±25%      | 8.0  | 9.0  | 10.7            | 8.2    |
| 2R5                | 2.50  | ±25%      | 7.0  | 8.4  | 11.8            | 9.1    |
| 3R0                | 3.00  | ±25%      | 6.3  | 6.6  | 17.3            | 13.3   |
| 3R9                | 3.90  | ±25%      | 6.0  | 6.2  | 19.1            | 14.7   |
| 4R5                | 4.50  | ±25%      | 5.4  | 5.8  | 20.8            | 16.0   |
|                    | a second a s |           |      |      | Color and Color | 111111 |

### **Environmental Characteristics - 3635A Series**

| Storage Temp:   | -55°C to +125°C                       |  |  |  |
|-----------------|---------------------------------------|--|--|--|
| Operating Temp: | -55°C to +105°C (Temp. rise included) |  |  |  |

## Reliability Test - 3635A Series

|                            |                      | 2010000000 00000  |  |  |
|----------------------------|----------------------|---|--|--|
| 'est Item                  | Specification        | Test Condition  |  |  |
| hermal Shock Test:         | $\Delta L \leq 20\%$ | Room Temp>> -25± 2°C  |  |  |
| Temp Cycle)                |                      | 15 minutes ->> 30 minutes   |  |  |
|                            |                      | Room Temp> 85± 2°C  |  |  |
|                            |                      | 15 minutes ->> 30 minutes   |  |  |
|                            |                      | Total: 50 cycles  |  |  |
| lumidity Resistance Test:  | ΔL ≤ 20%             | Temperature: 40± 2°C<br>Humidity: 90 ~ 95%<br>Applied Current: Per spec.<br>Time: 500 hours |  |  |
| igh Temp. Resistance Test: | ΔL ≤ 20%             | Temperature: 85± 2°C<br>Applied Current: Per spec.<br>Time: 500 hours                       |  |  |

### te.com

### 1773157 Rev. C 05/2023

© 2023 TE Connectivity. All Rights Reserved.





## Electrical Characteristics - 3635B Series

| Inductance | Initial<br>Inductance |      | Inductance<br>at Flat Point<br>L1 (µH) ±25 | Flat Point<br>Ref.<br>(A) | irms<br>(A) | lsat<br>(A) | DC Resistance (mΩ |      |  |
|------------|-----------------------|------|--|---------------------------|-------------|-------------|-------------------|------|--|
| Code       | LO (µH)               |      |  |                           |             |             | Max.              | Тур. |  |
| R30        | 0.54                  | ±25% | 0.30                                       | 5.00                      | 38.0        | 35.0        | 1.8               | 0.8  |  |
| R60        | 0.85                  | ±25% | 0.60                                       | 5.00                      | 28.0        | 27.0        | 2,5               | 1.5  |  |
| 1R0        | 1.25                  | ±25% | 1.00                                       | 5.00                      | 23.0        | 22,0        | 3.4               | 2,8  |  |
| 188        | 2.00                  | ±25% | 1.80                                       | 2.00                      | 20.0        | 16.0        | 3.4               | 2.5  |  |
| 2R5        | 2.70                  | ±25% | 2.50                                       | 2.00                      | 18.0        | 12.0        | 3.4               | 2.5  |  |
| 3R3        | 3.50                  | ±25% | 3.30                                       | 2.00                      | 16.0        | 11.8        | 5.4               | 4.3  |  |
| 4R0        | 4.20                  | ±25% | 4.00                                       | 2.00                      | 15.0        | 8.3         | 5.4               | 4.3  |  |
| 5R6        | 5.80                  | ±25% | 5.60                                       | 2.00                      | 12.0        | 8.0         | 11.4              | 9.2  |  |
| 7R2        | 7.40                  | ±25% | 7.20                                       | 2.00                      | 10.0        | 7.5         | 13.5              | 10.5 |  |

## **Environmental Characteristics - 3635B Series**

| Storage Temp:   | -40°C to +125°C                    |
|-----------------|------------------------------------|
| Operating Temp: | -40°C to +105°C                    |
| Rated Current:  | Base on temp. rise & AL/L=20% typ. |
| Temp. Rise:     | 40°C max.                          |

# Inductance Vs DC Superpostion Characteristics - 3635B Series



### te.com

## 1773157 Rev. C 05/2023

© 2023 TE Connectivity. All Rights Reserved.



# **Reliability Test - 3635B Series**

| Test Item                           | Specification   | Test Condition  |
|-------------------------------------|-----------------|---|
| Thermal Shock Test:<br>(Temp Cycle) | <u>ΔL</u> ≤ 20% | Room Temp> -25± 2°C<br>15 minutes -> 30 minutes   |
|                                     |                 | Room Temp. > 85± 2°C<br>15 minutes > 30 minutes   |
|                                     |                 | Total: 50 cycles  |
| Humidity Resistance Test:           | ΔL ≤ 20%        | Temperature: 40± 2°C<br>Humidity: 90 – 95%<br>Applied Current: Per spec.<br>Time: 500 hours |
| High Temp. Resistance Test:         | ΔL ≤ 20%        | Temperature: 105± 2°C<br>Applied Current: Per spec.<br>Time: 500 hours                      |

### Dimensions 3635B Series



| Series | A       | в       | D      | E        | E1       | E2       | F        | F1       | F2       | н         | 1         | J        | ĸ         | м        | N        | P        | P1        | P2        |
|--------|---------|---------|--------|----------|----------|----------|----------|----------|----------|-----------|-----------|----------|-----------|----------|----------|----------|-----------|-----------|
| 3635B  | 12.5±30 | 12.5±30 | 1.9±20 | 2.5 nom. | 2.0 ref. | 2.0 ref. | 7.5±0.25 | 6.4 ref. | 5.2 ref. | 10.5 ref. | 4.15 ref. | 3.0 ref. | 13.0 ref. | 4.7 rel. | 4.5 ref. | 7.5 ref. | 3.75 ref. | 3.75 ref. |

### te.com

1773157 Rev. C 05/2023

© 2023 TE Connectivity. All Rights Reserved.







| 3635                              | A  | R30                                       | P         | Ţ                       |  |
|-----------------------------------|--|---|-----------|-------------------------|--|
| Common Part                       | Style  | Inductance                                | Tolerance | Package                 |  |
| 3635 - Shielded<br>Power Inductor | A - 6.6mm x 6.6mm<br>x 4.5mm High<br>B - 12mm x 12mm<br>x 6mm High | See Relevant Table<br>for Inductance Code | P - 25%   | T - Taped and<br>Reeled |  |

While TE has made every reasonable effort to ensure the accuracy of the information in this Data Sheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

### te.com

1773157 Rev. C 05/2023

### © 2023 TE Connectivity. All Rights Reserved.