

Type MCN Series



The MCN is an innovative chip resistor network which combines a series of inline isolated 0402 or 0603 resistors into one package. Obvious savings in board space and number of placements are possible by specifying our resistor network packages.

The package layer design prevents tombstoning when reflow soldering the chips. Supplied on 8mm tape.

Key Features

- Concave and Convex Terminal Style
- Improved Placement Efficiency
- Superior Solderability
- Nickel Barrier Layer
- Individually Value Marked

PRODUCT
PLANNED FOR
EOL

LTB
18/08/2023

Type MCN Series


Characteristics - Electrical

Number of Elements:	4
Element Size:	0402 / 0603
Power Rating:	0.063W per resistor
Resistance Range:	10R - 1Meg ohm (E24 series) ±5% 100R - 560K ohm (E96 series) 0603 1% only
Resistance Tolerance:	±1% ±5% * Stock is ±5%
Temperature Coefficient of Resistance:	± 400ppm/°C
Max. Working Voltage:	50 volts
Operating Temperature Range:	-55°C to +155°C
Maximum Rated Temperature:	+ 70°C


Packaging

	5000 on reel
--	--------------

Dimensions -



Schematic



Model	No. of Elements	Element Size	Dimensions					
			A	B	C	D	E	F
MCNY4	4	0402	0.3±0.05	2.0±0.1	0.5±0.05	1.0±0.10	0.45±0.1	0.2±0.15
MCNT4	4	0603	0.5±0.15	3.2±0.2	0.8±0.1	1.6±0.20	0.60±0.1	0.3±0.15
MCNY4	4	0603	0.5±0.10	3.2±0.3	0.8±0.1	1.6±0.20	0.50±0.1	0.3±0.15

How to Order

Common Part	Element Size	Resistance Value	Tolerance
MCNT4 - 4 Resistors Concave MCNY4 - 4 Resistors Convex	1E - 0402 1J - 0603	103 <small>The first two digits are significant figures of resistance value. The third denotes the number of zeros following.</small> e.g. 1K: 102 50K - 503 100K - 104	F ±1% J ±5%* * Standard

While TE has made every reasonable effort to ensure the accuracy of the information in this Data Sheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.