

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

## General Information

<b>Extended Product Type:</b>	D95/26.YL
<b>Product ID:</b>	1SNA400791R0000
<b>EAN:</b>	3472594007913
<b>Catalog Description:</b>	D95/26.YL Screw Clamp Terminal Blocks - Feed-through - Yellow
<b>Long Description:</b>	- Closed terminal block: no end section needed, optimized rigidity, - Use of jumper bars requires the user to cut-out the partition.

## Ordering

<b>Color:</b>	Yellow
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160019C0202
<b>Instructions and Manuals:</b>	1SNC160019C0202

## Dimensions

<b>Product Net Width:</b>	26 mm
<b>Product Net Height:</b>	87 mm
<b>Product Net Depth / Length:</b>	72 mm
<b>Product Net Weight:</b>	215 g

## Technical

<b>Rated Cross-Section:</b>	95 mm <sup>2</sup>
<b>Spacing:</b>	26 mm
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Feed-through
<b>Number of Levels:</b>	1
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 35 ... 95 mm <sup>2</sup> Screw Clamp / Rigid 1x 35 ... 120 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 50 mm <sup>2</sup>
<b>Gauge Type:</b>	B12
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 232 A
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 11400 A
<b>Rated Voltage (U<sub>r</sub>):</b>	1000 V

<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8000 V
<b>Pollution Degree:</b>	3
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	26.0 mm
<b>Recommended Screw Driver:</b>	6 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 9 N·m Manufacturer 9.5 N·m

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 2 ... 0000 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 0 AWG

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

## Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	1SND161051A0202
<b>Declaration of Conformity - CE:</b>	1SND225014U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220001E1002
<b>Instructions and Manuals:</b>	1SNC160019C0202
<b>RMRS Certificate:</b>	1SND161007A1101

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	135 mm
<b>Package Level 1 Depth / Length:</b>	177 mm

<b>Package Level 1 Height:</b>	87 mm
<b>Package Level 1 Gross Weight:</b>	2.15 kg
<b>Package Level 1 EAN:</b>	3472594007913
<b>Package Level 2 Units:</b>	30 piece
<b>Package Level 2 Width:</b>	200 mm
<b>Package Level 2 Depth / Length:</b>	300 mm
<b>Package Level 2 Height:</b>	200 mm
<b>Package Level 3 Units:</b>	2880 piece
<b>Product Packing Type:</b>	Box

