

# MC612PA 161->170 (x10) Horizontal



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems  
→ Terminal Block Markers

## General Information

|                               |   |
|-------------------------------|---|
| <b>Extended Product Type:</b> | MC612PA 161->170 (x10) Horizontal   |
| <b>Product ID:</b>            | 1SNK150171R0000   |
| <b>EAN:</b>                   | 3472591501711   |
| <b>Catalog Description:</b>   | MC612PA Terminal Block Markers pre-printed : 161->170 (x10) Horizontal        |
| <b>Long Description:</b>      | MC612PA Terminal Block Markers pre-printed : 161->170 (x10) Horizontal White. |

## Ordering

|                                |          |
|--------------------------------|----------|
| <b>Color:</b>                  | White    |
| <b>Minimum Order Quantity:</b> | 1 piece  |
| <b>Customs Tariff Number:</b>  | 39269097 |

## Popular Downloads

|   |                 |
|---|-----------------|
| <b>Data Sheet, Technical Information:</b> | 1SNK160007D0201 |
| <b>Instructions and Manuals:</b>          | 1SNK160027C0201 |

## Dimensions

|                                    |        |
|------------------------------------|--------|
| <b>Product Net Width:</b>          | 6 mm   |
| <b>Product Net Height:</b>         | 12 mm  |
| <b>Product Net Length:</b>         | 5.6 mm |
| <b>Product Net Depth / Length:</b> | 5.6 mm |
| <b>Product Net Weight:</b>         | 11 g   |

## Technical

|                             |                         |
|-----------------------------|-------------------------|
| <b>Spacing:</b>             | 6 mm                    |
| <b>Function:</b>            | Pre-printed marker card |
| <b>Insulation Material:</b> | Polyamide               |

## Technical UL/CSA

|  |    |
|--|----|
| <b>Flammability According to UL94:</b> | V2 |
|--|----|

## Environmental

|                                 |  |
|---------------------------------|--|
| <b>Ambient Air Temperature:</b> | Operation -55 ... +110 °C<br>Storage -55 ... +110 °C |
|---------------------------------|--|

**RoHS Status:**

Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

**Declaration of Conformity - CE:** 1SND225156C1000

**Environmental Information:** 1SND220060E1000

**Instructions and Manuals:** 1SNK160027C0201

**RoHS Information:** 1SND230504F0204

## Classifications

**Object Classification Code:** X

**E-number:** 2967627

**ETIM 4:** EC000761 - Labelling for terminal block

**ETIM 5:** EC000761 - Labelling for terminal block

**ETIM 6:** EC000761 - Labelling for terminal block

## Container Information

**Package Level 1 Units:** 1 piece

**Package Level 1 Width:** 120 mm

**Package Level 1 Depth / Length:** 200 mm

**Package Level 1 Gross Weight:** 0.011 kg

**Package Level 1 EAN:** 3472591501711

**Package Level 2 Units:** 600 piece

**Package Level 3 Units:** 14400 piece

