

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks  
→ Railway Terminal Blocks

## General Information

<b>Extended Product Type:</b>	HD6/9.5G
<b>Product ID:</b>	1SNA160621R0200
<b>EAN:</b>	3472591606218
<b>Catalog Description:</b>	HD6/9.5G - Quick-connect terminal blocks - 5 tabs - Beige
<b>Long Description:</b>	- Connection by 5 vertical tabs for quick-connect 6.3 x 0.8 mm 0.248 x 0.031 in, - Possibility of testing and transverse connection, - Use of jumper bars requires to cut out the precut partition, - NF F 61-017 designation: BC000 9-3G2G (1SNA160621R0200).

## Ordering

<b>Color:</b>	Beige
<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0205_CHD3
<b>Instructions and Manuals:</b>	1SNC160001C0205_CHD3

## Dimensions

<b>Product Net Width:</b>	9 mm
<b>Product Net Height:</b>	61.5 mm
<b>Product Net Depth / Length:</b>	29.5 mm
<b>Product Net Weight:</b>	13 g

## Technical

<b>Rated Cross-Section:</b>	6 mm <sup>2</sup>
<b>Spacing:</b>	9 mm
<b>Connection Type:</b>	Quick-connect
<b>Function:</b>	Feed-through
<b>Number of Levels:</b>	1
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 25 A
<b>Dielectric Test Voltage:</b>	2950 V
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide

<b>Mounting on DIN Rail:</b>	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
------------------------------	--

## Technical UL/CSA

<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
------------------------------------	-----------------

<b>Flammability According to UL94:</b>	V0
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225001U1000
--	-----------------

<b>EAC Certificate:</b>	1SND161009A1100
-------------------------	-----------------

<b>Environmental Information:</b>	1SND220040E1002
-----------------------------------	-----------------

<b>Instructions and Manuals:</b>	1SNC160001C0205_CHD3
----------------------------------	----------------------

<b>RoHS Information:</b>	1SND230014F0202
--------------------------	-----------------

## Classifications

<b>Object Classification Code:</b>	X
------------------------------------	---

<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
----------------	--

<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
----------------	--

<b>ETIM 6:</b>	EC000897 - Feed-through terminal block
----------------	--

## Container Information

<b>Package Level 1 Units:</b>	25 piece
-------------------------------	----------

<b>Package Level 1 Width:</b>	70 mm
-------------------------------	-------

<b>Package Level 1 Depth / Length:</b>	225 mm
--	--------

<b>Package Level 1 Height:</b>	42 mm
--------------------------------	-------

<b>Package Level 1 Gross Weight:</b>	0.325 kg
--------------------------------------	----------

<b>Package Level 1 EAN:</b>	3472591606218
-----------------------------	---------------

<b>Package Level 2 Units:</b>	500 piece
-------------------------------	-----------

<b>Package Level 2 Width:</b>	300 mm
-------------------------------	--------

<b>Package Level 2 Depth / Length:</b>	500 mm
--	--------

<b>Package Level 2 Height:</b>	150 mm
--------------------------------	--------

<b>Package Level 3 Units:</b>	24000 piece
-------------------------------	-------------

<b>Product Packing Type:</b>	Box
------------------------------	-----

