ZS6-S-4S-T2



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks + SNK Series

General Information

Extended Product Type: ZS6-S-4S-T2

Product ID: 1SNK506316R0000 EAN: 3472595063161

Catalog Description: ZS6-S-4S-T2 Screw Clamp Terminal Block - Disconnect with blade - Grey

Long Description: - Recommended for energy markets and highly demanding applications re

quiring that only one conductor be connected per clamp, - Ease your disconnect and test operations with the two built-in test socket screws, - Simplify

the alternated distribution thanks to the jumper channel.

Ordering

Color: Grey

Minimum Order Quantity: 50 piece

Customs Tariff Number: 85369010

Popular Downloads

Data Sheet, Technical Information: 1SNK161066D0201

Instructions and Manuals: 1SNK160027C0201

Dimensions

Product Net Width: 6 mm

Product Net Height: 80.7 mm

Product Net Length: 51.4 mm

Product Net Depth / Length: 51.4 mm

Product Net Weight: 18.4 g

Technical

Rated Cross-Section: 4 mm²

Spacing: 6 mm

Connection Type: Screw clamp

Function: Disconnect

Number of Levels: 1

Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 6 mm ² Screw Clamp / Flexible 2x 0.2 2.5 mm ² Screw Clamp / Rigid 1x 0.2 6 mm ² Screw Clamp / Rigid 2x 0.2 2.5 mm ² Screw Clamp / With Insulated Ferrule 1x 0.22 4 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.22 4 mm ² Screw Clamp / With Twin Ferrule 2x 0.22 2.5 mm ²
Gauge Type:	A4-B3
Rated Current (I _n):	Main Circuit 27 A
Rated Short-time Withstand Current (I _{cw}):	for 1 s 480 A
Rated Voltage (U _r):	500 V
Rated Impulse Withstand Voltage (U _{imp}):	6000 V
Dielectric Test Voltage:	1890 V
Pollution Degree:	3
Power Loss:	1.7 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.5 mm
Recommended Screw Driver:	4 mm
echnical UL/CSA	
Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 24 10 AWG Screw Clamp / Rigid 2x 24 14 AWG Screw Clamp / With Insulated Ferrrule 1x 24 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 12 AWG Screw Clamp / With Twin Ferrule 2x 24 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0
nvironmental	
Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
Resistance to Vibrations acc. to	Compliant
IEC 60068-2-6:	

Certificates and Declarations (Document Number)

BV Certificate:	1SND161073A0204
CB Certificate:	1SND161096A0200
CSA Certificate:	1SND161070A0209
cUL Certificate:	1SND161041A0210
Declaration of Conformity - CE:	1SND225102U1000
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220171E0200
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230491F0206

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	172 mm
Package Level 1 Depth / Length:	155 mm
Package Level 1 Height:	71 mm
Package Level 1 Gross Weight:	0.97 kg
Package Level 1 EAN:	3472595063161
Package Level 2 Units:	300 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	5.820 kg
Package Level 3 Units:	14400 piece
Product Packing Type:	Box

