

ZK4-4P-OR



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

General Information

| | |
|-------------------------------|--|
| Extended Product Type: | ZK4-4P-OR |
| Product ID: | 1SNK706032R0000 |
| EAN: | 3472597060328 |
| Catalog Description: | ZK4-4P-OR PI-Spring clamp Terminal Block - Feed-through - Orange |
| Long Description: | Find all the features of the ZK4 terminal block with the added option of distributing or branching 4 conductors. |

Ordering

| | |
|--------------------------------|----------|
| Color: | Orange |
| Minimum Order Quantity: | 50 piece |
| Customs Tariff Number: | 85369010 |

Popular Downloads

| | |
|---|-----------------|
| Data Sheet, Technical Information: | 1SNK162027D0201 |
| Instructions and Manuals: | 1SNK160027C0201 |

Dimensions

| | |
|------------------------------------|---------|
| Product Net Width: | 6 mm |
| Product Net Height: | 89.7 mm |
| Product Net Length: | 41.1 mm |
| Product Net Depth / Length: | 41.1 mm |
| Product Net Weight: | 13.8 g |

Technical

| | |
|--|---|
| Rated Cross-Section: | 4 mm ² |
| Spacing: | 6 mm |
| Connection Type: | PI Spring |
| Function: | Feed-through |
| Number of Levels: | 1 |
| Connecting Capacity Main Circuit: | Spring Clamp / Flexible 1x 0.5 ... 4 mm ² Spring Clamp / Rigid 1x 0.5 ... 6 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 4 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 4 mm ² Spring Clamp / With Twin Ferrule 2x 0.5 ... 1 mm ² |
| Gauge Type: | 2.9 mm Dia. |
| Rated Current (I_n): | Main Circuit 32 A |

| | |
|--|--|
| Rated Short-time Withstand Current (I_{cw}): | for 1 s 480 A |
| Rated Voltage (U_r): | 1000 V |
| Rated Impulse Withstand Voltage (U_{imp}): | 8000 V |
| Dielectric Test Voltage: | 2200 V |
| Pollution Degree: | 3 |
| Power Loss: | 1 W |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material: | Polyamide |
| Mounting on DIN Rail: | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Wire Stripping Length: | 12.5 mm |

Technical UL/CSA

| | |
|---|--|
| Maximum Operating Voltage UL/CSA: | Main Circuit 600 V |
| Connecting Capacity Main Circuit UL/CSA: | Spring Clamp / Rigid 1x 26 ... 10 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 12 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 12 AWG |
| Connecting Capacity UL/CSA: | Stranded 10 AWG |
| Flammability According to UL94: | V0 |
| Short-Circuit Current Rating (SCCR): | 100 kA |

Environmental

| | |
|--|--|
| Ambient Air Temperature: | Operation -55 ... +110 °C Storage -55 ... +110 °C |
| Resistance to Vibrations acc. to IEC 60068-2-6: | Compliant |
| RoHS Status: | Following EU Directive 2011/65/EU |

Certificates and Declarations (Document Number)

| | |
|--|-----------------|
| ATEX Certificate: | 1SND162009A1702 |
| BV Certificate: | 1SND162013A0203 |
| CB Certificate: | 1SND162016A0200 |
| CSA Certificate: | 1SND162014A0206 |
| cUL Certificate: | 1SND162012A0204 |
| Declaration of Conformity - CE: | 1SND225112U1004 |
| DNV Certificate: | 1SND162023A0200 |
| EAC Certificate: | 1SND161010A1100 |

Environmental Information: 1SND220072E1002

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230535F0201

Classifications

Object Classification Code: X

ETIM 4: EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 92 mm

Package Level 1 Depth / Length: 302 mm

Package Level 1 Height: 43 mm

Package Level 1 Gross Weight: 0.74 kg

Package Level 1 EAN: 3472597060328

Package Level 2 Units: 600 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 8.88 kg

Package Level 3 Units: 28800 piece

Product Packing Type: Box

