

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	D95/26.N
Product ID:	1SNA400371R1100
EAN:	3472594003717
Catalog Description:	D95/26.N Screw Clamp Terminal Blocks - Feed-through - Blue
Long Description:	- Closed terminal block: no end section needed, optimized rigidity, - Use of jumper bars requires the user to cut-out the partition.

Ordering

Color:	Blue
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	26 mm
Product Net Height:	87 mm
Product Net Depth / Length:	72 mm
Product Net Weight:	215 g

Technical

Rated Cross-Section:	95 mm ²
Spacing:	26 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 35 ... 95 mm ² Screw Clamp / Rigid 1x 35 ... 120 mm ² Screw Clamp / With Insulated Ferrule 1x 50 mm ²
Gauge Type:	B12
Rated Current (I_n):	Main Circuit 232 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 11400 A
Rated Voltage (U_r):	1000 V

Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	26.0 mm
Recommended Screw Driver:	6 mm
Tightening Torque:	acc. IEC 60947-1 9 N·m Manufacturer 9.5 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 2 ... 0000 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 2 ... 0000 AWG Stranded 0 AWG

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161051A0202
cUL Certificate:	1SND161009A0202
Declaration of Conformity - CE:	1SND225014U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220001E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Width:	135 mm
Package Level 1 Depth / Length:	177 mm
Package Level 1 Height:	87 mm
Package Level 1 Gross Weight:	2.15 kg
Package Level 1 EAN:	3472594003717
Package Level 2 Units:	30 piece
Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	2880 piece
Product Packing Type:	Box

