

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	D70/22.P
Product ID:	1SNA400772R1300
EAN:	3472594007722
Catalog Description:	D70/22.P Screw Clamp Terminal Blocks - Ground - Green-Yellow
Long Description:	Reliable electrical and mechanical contact with the rail.

Ordering

Color:	Green-Yellow
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	22 mm
Product Net Height:	74 mm
Product Net Depth / Length:	68.8 mm
Product Net Weight:	222 g

Technical

Rated Cross-Section:	70 mm ²
Spacing:	22 mm
Connection Type:	Screw clamp
Function:	Ground
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 16 ... 70 mm ² Screw Clamp / Rigid 1x 16 ... 95 mm ² Screw Clamp / With Insulated Ferrule 1x 50 mm ²
Gauge Type:	B11
Rated Short-time Withstand Current (I_{cw}):	for 1 s 8400 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V

Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	25.0 mm
Recommended Screw Driver:	6 mm
Tightening Torque:	acc. IEC 60947-1 6 N·m Manufacturer 7 N·m

Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 4 ... 00 AWG Screw Clamp / Rigid 1x 4 ... 00 AWG Screw Clamp / With Insulated Ferrule 1x 2 ... 0 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 4 ... 00 AWG Stranded 0 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161051A0202
cUL Certificate:	1SND161001A0209
Declaration of Conformity - CE:	1SND225017U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220004E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101

Classifications

Object Classification Code:	X
ETIM 4:	EC000901 - Ground terminal block
ETIM 5:	EC000901 - Ground terminal block
ETIM 6:	EC000901 - Ground terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	135 mm

Package Level 1 Depth / Length:	175 mm
Package Level 1 Height:	74 mm
Package Level 1 Gross Weight:	2.22 kg
Package Level 1 EAN:	3472594007722
Package Level 2 Units:	80 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	3840 piece
Product Packing Type:	Box

