

PC-RG25-2



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Lateral Jumper Bars

General Information

Extended Product Type:	PC-RG25-2
Product ID:	1SNA519106R0200
EAN:	3472595191062
Catalog Description:	PC-RG25M6-2 Ring lug Lateral Jumper Bar - 2 poles - Orange
Long Description:	- Lateral jumper bar for ring lug terminal block, - Allow the connection of consecutive blocks, - Compatible with RGW terminal block of 18 mm 0.709 in spacing

Ordering

Color:	Orange
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	3.6 mm
Product Net Height:	26.6 mm
Product Net Depth / Length:	33.3 mm
Product Net Weight:	8.81 g

Technical

Spacing:	18 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 101 A
Rated Voltage (U_r):	800 V
Power Loss:	3.2 W
Insulation Material:	Polyamide
Suitable For:	RGW25-M5 RGW25-M6

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -40 ... +100 °C Storage -40 ... +100 °C
RoHS Status:	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225158C1001
Environmental Information:	1SND220070E1001
RoHS Information:	1SND230547F0201

Classifications

ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	58 mm
Package Level 1 Depth / Length:	47 mm
Package Level 1 Height:	80 mm
Package Level 1 Gross Weight:	0.245 kg
Package Level 1 EAN:	3472595191062
Product Packing Type:	Box

