

DATA SHEET - HOLLOW SHAFT RESOLVER


PN	2360964-1					
Description:		V23401-	T2079-B101			
Size	21					
Shaft inner diameter [mm]	12.7					
Speed (pair of poles) [p]	1					
Number of poles	2					
Application Specification						
Test protocol	Result	s saved to manufactu	uring site archives. Available by reque	st		
Electrical parameters (22°C)						
Input voltage [V]	5		Input resistance R1R2 [Ω]	30		
Frequency Typical [kHz]	4		R1R2 tolerance [%]	± 10		
Input current max [mA]	50	Based on specified Input voltage and Frequency	Output resistance S1S3 or S2S4 [Ω]	46		
Transformation ratio (rT)	0.5		S1S3 or S2S4 tolerance [%]	± 10		
Transf. ratio tolerance [%]	± 10					
Phase shift min [º]	1					
Phase shift max [º]	11					
Electrical Angular Error max [']	± 10					
Residual voltage max [mV]	15					
		5001/ (4)				
High Voltage test	Voltage: 500V _{AC} (A)		Measured between:			
	250V _{AC} (B)		A: Winding R1-R2 and housing			
	Time: 1s		Winding S1-S3 and housing Winding S2-S4 and housing			
Isolation test	Voltage: 500V _{DC} (A, B)					
	Criterium:	$R_{isol.} > 50M\Omega$	B: Windings S1-S3 and S2-S4			
"Zero" setting:	Electrical "0" is when Coils $V_{\rm S2-S4}$ = 0 and $V_{\rm S1-S3}$ are in phase with $V_{\rm R1-R2}$					
Transfer function	Looking at Transformation part and turning Rotor clockwise					
	V _{S1-S3} =+rT * V _{R1-R2} * cos(p*α)					
	$V_{S2-S4} = +rT * V_{R1-R2} * sin(p*\alpha)$					
Rotor Inertia	approx. 20g.cm ²					
Max. Rotational Speed	20,000 rpm					
Shock resistance						
(11ms sine)	1000 m/s ²					
Vibration	200 m/s ²					
Operating temp.	-55°C+150°C					

© 2019 TE Connectivity family of companies

| Indicates Change

*Trademark. TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

All Rights Reserved



Gesamtschlag im eingebauten Zustand Concentricity in installed situation

Axialversatz Axial displacement/offset

DATE	<u>PN. REV.</u>	<u>DWN</u>	APP	<u>DS.</u> REV.
22-01-20	1	H.Bernardo	D.Ondrej	1

Page 2/2