

TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks + SNK Series

General Information

Extended Product Type: ZS70

Product ID: 1SNK522010R0000 **EAN**: 3472595220106

Catalog Description: ZS70 Screw Clamp Terminal Block - Feed-through - Grey

Long Description: Closed terminal block: - No end section needed, - Optimized rigidity, - Perf

ectly adapted to solar applications: 1250 V DC (1000 V AC) IEC and 1000

V UL.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK161021D0201

Instructions and Manuals: 1SNK160027C0201

Dimensions

Product Net Width:	22 mm
Product Net Height:	74 mm
Product Net Length:	75.35 mm
Product Net Depth / Length:	75.4 mm
Product Net Weight:	158.1 a

Technical

Rated Cross-Section:	70 mm²
Spacing:	22 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 16 70 mm²
	Screw Clamp / Flexible 2x 16 35 mm²
	Screw Clamp / Rigid 1x 16 95 mm²
	Screw Clamp / Rigid 2x 16 35 mm²
	Screw Clamp / With Insulated Ferrrule 1x 16 50 mm²

Screw Clamp / With Twin Ferrule 2x 16 mm²

Screw Clamp / Without Insulated Ferrule 1x 16 ... 50 mm²

Gauge Type:	B11
Rated Current (I _n):	Main Circuit 192 A
Rated Short-time Withstand Current (I _{cw}):	for 1 s 8400 A
Rated Voltage (U _r):	1000 V
Rated Impulse Withstand Voltage U _{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	6.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
nsulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	25.0 mm
Recommended Screw Driver:	6 mm
chnical UL/CSA	
Maximum Operating Voltage UL/CSA:	Main Circuit 1000 V

Te

UL/CSA:	Main Circuit 1000 V	
Connecting Capacity Main Circuit	Screw Clamp / Flexible 1x 4 00 AWG	
UL/CSA:	Screw Clamp / Flexible 2x 4 2 AWG	
	Screw Clamp / Rigid 1x 4 00 AWG	
	Screw Clamp / Rigid 2x 4 2 AWG	
	Screw Clamp / With Twin Ferrule 2x 6 AWG	
Connecting Capacity UL/CSA:	Stranded 0 AWG	
Flammability According to UL94:	V0	
Short-Circuit Current Rating	100 kA	
(SCCR):		

Environmental

Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162004A1708
BV Certificate:	1SND161073A0204
CB Certificate:	1SND161034A0202
CSA Certificate:	1SND161070A0209

cUL Certificate:	1SND161040A0206
Declaration of Conformity - CE:	1SND225112U1004
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220071E1000
Instructions and Manuals:	1SNK160027C0201
RINA Certificate:	1SND161088A0200
RMRS Certificate:	1SND161008A1101
RoHS Information:	1SND230491F0206

Classifications

Object Classification Code:	X
E-nummer:	2925982
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	138 mm
Package Level 1 Depth / Length:	151 mm
Package Level 1 Height:	78 mm
Package Level 1 Gross Weight:	1.581 kg
Package Level 1 EAN:	3472595220106
Package Level 2 Units:	30 piece
Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	4.743 kg
Package Level 3 Units:	3840 piece
Product Packing Type:	Box

