

2385446-1 ✓ ACTIVE

TE Internal #: 2385446-1

Housing for Female Terminals, Wire-to-Wire, 28 Position, Black,
Wire & Cable, Cable Mount (Free-Hanging), Key A-D

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**

Number of Positions: **28**

Connector & Housing Type: **Housing for Female Terminals**

Sealable: **No**

Mating Tab Width: **.64 mm, 1.2 mm, 2.8 mm [.025 in, .047 in, .11 in]**

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	28
Number of Rows	3

Body Features

Primary Product Color	Black
Connector & Keying Code	A-D

Contact Features

Contact Size	.64mm, 1.2mm, 2.8mm
Contact Type	Receptacle



Mating Tab Width	.64 mm, 1.2 mm, 2.8 mm [.025 in][.047 in][.11 in]
------------------	---

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

28POS, HYBRID, REC HSG ASSY, UNSLD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2385446-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2385446-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2385446-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[28P Hybrid Inline Unsealed Connector Design Objective](#)

English

[28P Hybrid Inline Unsealed Connector Application](#)

English