

344267-1 ✓ ACTIVE

AMP | Econoseal


TE Internal #: 344267-1

Receptacle, 6 Position, .188 in [4.8 mm] Centerline, Sealable, Black,
Wire & Cable, Cable Mount (Free-Hanging), Econoseal

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 6

Connector & Housing Type: **Receptacle**

Centerline (Pitch): 4.8 mm [.188 in]

Sealable: **Yes**

Number of Rows: 2

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector & Housing Type	Receptacle
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	6
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	4.8 mm[.188 in]
--------------------	-----------------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2023 (235)</p> <p>Candidate List Declared Against: JUNE 2023 (235)</p> <p>SVHC > Threshold:</p> <p>Octamethylcyclotetrasiloxane (D4) (.11% in Component Part)</p> <p>Dodecamethylcyclohexasiloxane (D6) (.11% in Component Part)</p> <p>Decamethylcyclopentasiloxane (D5) (.11% in Component Part)</p> <p>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 345260-1
ANTI-BACKOUT 6WAY REC
HSGECONO




TE Part # 347705-1
6 WAY PERIPHERAL SEAL SILIC

Also in the Series | Econoseal



Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(25)



Automotive Housings(86)



Automotive Terminals(43)




Connector Seals & Cavity Plugs(16)



Insertion & Extraction Tools(7)



Other Automotive Connector Accessories(5)



PCB Headers & Receptacles(3)



Primary Wire(1)


Customers Also Bought



TE Part #1-967624-4
JUN-POW-TIM GEH 18P



TE Part #344265-1
6 WAY TAB HSG.- BLACK ECONO




TE Part #345164-1
040 SERIES TAB



TE Part #1718762-1
MCON 1.2 LL TAB SWS SN



TE Part #345260-1
ANTI-BACKOUT 6WAY REC HSGECONO



TE Part #344112-1
36W EMS.REC.ANTI-BACKOUT



TE Part #344274-1
2 WAY TAB HOUSING BLACK ECONO



TE Part #345259-1
ANTI-BACKOUT 6WAY TAB HSGECONO



Documents

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_344267-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_344267-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_344267-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.