
344276-1 - ACTIVE

AMP | Econoseal TE Internal #: 344276-1 Wire-to-Wire, 2 Position, .188 in [4.8 mm] Centerline, Sealable, Black, Wire & Cable, Cable Mount (Free-Hanging), Econoseal View on TE.com >



Connectors > Automotive Connectors > Automotive Housings



Connector System: Wire-to-Wire

Number of Positions: 2

Centerline (Pitch): 4.8 mm [.188 in]

Sealable: Yes

Number of Rows: 1

Features

Product Type Features

Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2				
Number of Rows	1				
Body Features					
Primary Product Color	Black				
Mechanical Attachment					
Connector Mounting Type	Cable Mount (Free-Hanging)				
Housing Features					
Centerline (Pitch)	4.8 mm[.188 in]				
Product Compliance For compliance documentation, visit the product page on TE.com>					
EU RoHS Directive 2011/65/EU	Compliant				
EU ELV Directive 2000/53/EC	Compliant				

C For support call+1 800 522 6752

344276-1

Wire-to-Wire, 2 Position, .188 in [4.8 mm] Centerline, Sealable, Black, Wire & Cable, Cable Mount (Free-Hanging), Econoseal



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC	
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free	
Solder Process Capability	Not applicable for solder process capability	


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




Also in the Series | Econoseal




344276-1


Wire-to-Wire, 2 Position, .188 in [4.8 mm] Centerline, Sealable, Black, Wire & Cable, Cable Mount (Free-Hanging), Econoseal







Customers Also Bought



TE Part #5-1624112-9 3650 0603 1.6nH 5% 2K RL	TE Part #344270-1 4 WAY REC.HSG. SIL. SEAL ECONO	TE Part #174515-1 040/070 HYBRID PLUG 22P WHITE	TE Part #345806-1 ECONO CONTACT REC
TE			onthe Signature
TE Part #3-1462000-7 C93418=MT Relay 200 mW 12 V	TE Part #345257-1 ANTI-BACKOUT 4WAY TAB HSGECONO	TE Part #345254-1 ANTI-BACKOUT 2WAY REC HSGECONO	TE Part #347874-1 CABLE SEAL LC SILICON 0.5 T



Documents

344276-1

Wire-to-Wire, 2 Position, .188 in [4.8 mm] Centerline, Sealable, Black, Wire & Cable, Cable Mount (Free-Hanging), Econoseal



Product Drawings 2 WAY REC HSG. SIL SEAL ECONO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_344276-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_344276-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_344276-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.