



379 CABLE ASSEMBLY

Instrumentation cable for the model 140A & 142A in-line amplifiers. Featuring shielded model 712 series Binder connector to pigtail leads. Standard cable length is 120 inches.


FEATURES

- TPE Jacket
- PFA Insulated #30 AWG Conductors
- SPC Braided Shield
- Shielded Connector
- -40°C to +85°C Temp Range


APPLICATIONS

- In-line Amplifiers
- Laboratory Testing
- Vibration Monitoring
- General Purpose

DIMENSIONS



SCHEMATIC



ORDERING INFORMATION

379 - ZZZ

Cable length

120=120 inches

240=240 inches

360=360 inches

Example; 379-120

Model 379 cable, 120inch cable length (standard length typically in stock)

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.akn@te.com

EUROPE

MEAS France SAS
a TE Connectivity Company
Tel: +31 73 624 6999
customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.shzn@te.com

te.com/sensorsolutions

TE Connectivity, TE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, products and/or company names referred to herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.