



# 12-PORT EN50155 POE RACK ETHERNET SWITCH

## GIGABIT RACK MOUNT MANAGED ETHERNET SWITCH

TE's EN50155 compliant Ethernet switches are designed for industrial applications such as rolling stock, vehicle, and railway. The 2352906, is a managed 2.5/10 Gigabit Redundant Ring Ethernet switch with 8x10/100/1000Base-T(X) P.S.E. and 4x1G/2.5G/5G/10GBase-T ports which is specifically designed for the toughest conditions. The switch supports the Ethernet Redundancy protocol, a recovery time < 30ms over 250 units of connection, MSTP (RSTP/STP compatible), it protects your mission-critical applications from network interruptions or temporary malfunctions with its fast recovery technology. The Ethernet switch uses M12X connectors to ensure tight, robust connections, and guarantee reliable operation. It also supports Power over Ethernet. Each switch has 8x10/100/1000Base-T(X) P.S.E. (Power Sourcing Equipment) ports. The Switch is easily managed using TE-vision, Telnet, CLI or its web-based interface.

#### **Technical Drawing**







#### **Product Features:**

- TE-Ring: TE-Ring is redundant ring technology, with recovery time of less 30 milliseconds and up to 250 nodes. The TE-Ring redundant ring technology can protect mission-critical application from network interruptions or temporary malfunction with its fast recover technology.
- **TE-Chain**: TE-Chain is the revolutionary network redundancy technology that provides the add-on network redundancy topology for any backbone network, TE-Chain allows multiple redundant network rings of different redundancy protocols to join and function together as a larger and more robust compound network topology. TE-Chain providing ease-of-use while maximizing fault-recovery swiftness, flexibility, compatibility, and cost-effectiveness in one set of network redundancy topology.
- IP-based Bandwidth Management: The switch provide advanced IP-based bandwidth management which can limit the maximum bandwidth for each IP device. User can configure IP camera and NVR with more bandwidth and limit other device bandwidth.
- Application-Based QoS: The switch also support application-based QoS. Application-based QoS can set highest priority for data stream according to TCP/UDP port number.
- Device Binding Function: Special Device Binding function can only permit allowed IP address with MAC address to access the network. Hacker cannot access the IP surveillance network without permission. It can avoid hacker from stealing video privacy data and attacking IP camera, NVR and controllers.
- Advanced DOS/DDOS Auto Prevention: The switch also provided advanced DOS/DDOS auto prevention. If there is any IP flow become big in short time, the switch will lock the source IP address for certain time to prevent the attack. It's hardware based prevention so it can prevent DOS/DDOS attack immediately and completely.
- **IEEE 1588v2 Technology**: The IEEE 1588v2 technology can fulfill precision time synchronization requirements for protection and control applications.
- Modbus TCP: This is a Modbus variant used for communications over TCP/IP networks.
- **IEEE 802.3az Energy-Efficient Ethernet**: This is a set of enhancements to the twisted-pair and backplane Ethernet family of networking standards that will allow for less power consumption during periods of low data activity. The intention was to reduce power consumption by 50% or more.

# 12-PORT EN50155 MANAGED GIGABIT POE ETHERNET SWITCH

Part Number		
	2352906-1	2352906-2
Physical ports		
10/100/1000 Base-T(X) Ports in M12 Auto MDI/MDIX	12 x M12 connector (8-pin M12 female X-coding), 8 ports with P.S.E.	8 x M12 connector (8-pin M12 female X-coding) with P.S.E.
1G/2.5G/5G/10GBase-T ports in M12 Auto MDI/MDIX	-	4 x M12 connector (8-pin M12 female X-coding)
Bypass	2 x bypass function	
Technology		
Ethernet Standards	IEEE 802.3 for 10Base-T IEEE 802.3u for 100Base-TX IEEE 802.3b for 1000Base-T IEEE 802.3bz for 2.5GBase-T IEEE 802.3an for 10GBase-T IEEE 802.3x for Flow control IEEE 802.3ad for LACP (Link Aggregation Control Protocol) IEEE 802.1p for COS (Class of Service) IEEE 802.1Q for VLAN Tagging IEEE 802.1W for RSTP (Rapid Spanning Tree Protocol) IEEE 802.1s for MSTP (Multiple Spanning Tree Protocol) IEEE 802.1x for Authentication IEEE 802.1AB for LLDP (Link Layer Discovery Protocol) IEEE 802.3at PoE specification (up to 30 Watts per port for P.S.E.)	
MAC Table	8k	
Priority Queues	8	
Processing	Store-and-Forward	
Switch Properties	Switching latency: 7 us Switching bandwidth: 2352906-1, 24Gbps; 2352906-2, 96 Gbps Max. Number of Available VLANs: 4095 IGMP multicast groups: 128 for each VLAN Port rate limiting: User Define	
Jumbo frame	Up to 9.6K Bytes	
Security Features	Device Binding security feature Enable/disable ports, MAC based port security Port based network access control (802.1x) VLAN (802.1Q) to segregate and secure network traffic Radius centralized password management SNMPv3 encrypted authentication and access security Https / SSH enhance network security	
Software Features	STP/RSTP/MSTP (IEEE 802.1D/w/s) Redundant Ring (O-Ring) with recovery time less than 30ms over 250 units TOS/Diffserv supported Quality of Service (802.1p) for real-time traffic VLAN (802.1Q) with VLAN tagging and GVRP supported IGMP Snooping IP-based bandwidth management Application-based QoS management	



## 12-PORT EN50155 MANAGED GIGABIT POE ETHERNET SWITCH

Software Features	DOS/DDOS auto prevention Port configuration, status, statistics, monitoring, security DHCP Server/Client/Relay SMTP Client Modbus TCP	
Network Redundancy	TE-Ring TE-Chain MSTP (RSTP/STP compatible)	
RS-232 Serial Console Port	RS-232 in M12 (5-pin female A-coding) connector with console cable. 115200bps, 8, N, 1	
LED Indicators		
Power Indicator (PWR)	Green: Power LED x 1	
Ring Master Indicator (R.M.)	Green : Indicates that the system is operating in TE-Ring Master mode	
TE-Ring Indicator (Ring)	Green : Indicates that the system operating in TE-Ring mode Green Blinking : Indicates that the Ring is broken.	
Fault Indicator (Fault)	Amber : Indicate unexpected event occurred	
10/100/1000Base-T(X) M12 P.S.E. Port Indicator	Top dual color LED for Ethernet speed indicator : Green LED for 1Gbps, Amber for 100Mbps, Off for 10Mbps Middle Green LED for PoE enable indicator Bottom Green LED for port Link/Act indicator	
2352906-1: 10/100/1000Base-T(X) M12 Port Indicator	Top dual color LED for Ethernet speed indicator: Green LED for 1000Mbps, Amber for 100Mbps, Off for 10Mbps Bottom Green LED for Link/Act indicato	
2352906-2: 1G/2.5G/5G/10GBase-T M12 Port Indicator	Top dual color LED for Ethernet speed indicator : Green LED for 10Gbps, Amber for 1Gbps. Middle Dual color LED for Ethernet speed indicator Bottom Green LED for port Link/Act indicator	
Fault contact		
Relay	Relay output to carry capacity of 3A at 24VDC on M12 connector (5-pin female A-coding)	
Power		
Redundant Input Power	72/96/110VDC (50.4-154VDC) on 4-pin S-coding, male M12 connector	
Power consumption (Typ.)	20 Watts (power consumption of P.S.E. is not included)	41 Watts (power consumption of P.S.E. is not included)
Total PoE Output Power	60 Watts	
Overload current protection	Present	
Reverse Polarity Protection	Present	
Physical Characteristics		
Enclosure	IP-30	
Dimensions (WxDxH) in mm	438 (W) x 250 (D) x 44 (H)	
Weight (g)	3185	3919



## 12-PORT EN50155 MANAGED GIGABIT POE ETHERNET SWITCH

Environmental		
Storage Temperature	-40 to 85°C (-40 to 185°F)	
Operating Temperature	-40 to 75°C (-40 to 167°F)	
Operating Humidity	5% to 95% Non-condensing	
Regulatory Approvals		
EMI	FCC Part 15, CISPR (EN55022) class A, EN50155 (EN50121-3-2, EN550121-1)	
EMS	EN61000-4-2 (ESD), EN61000-4-3 (RS), EN61000-4-4 (EFT), EN61000-4-5 (Surge), EN61000-4-6 (CS), EN61000-4-8, EN61000-4-11	
Shock and Free Fall	IEC60068-2-27, IEC60068-2-32	
Vibration	IEC60068-2-6	
Safety	EN60950-1	
Other	EN 50155 (IEC 61373)	