

REV. 1
DCO 170580


COIL: @ 25°C
 RESISTANCE _____ 2500 OHMS ±10%
 NOMINAL VOLTAGE _____ 8.0 mADC
 MUST OPERATE _____ 4.0 mADC

 MUST RELEASE _____ 2.0 mADC MAX, 0.4 mADC MIN.

ENVIRONMENT:
 VIBRATION _____ 10 _____ CPS TO _____ 2000 _____ CPS @ _____ 15 _____ g's
 SHOCK _____ 100 _____ g's _____ 6 ± 1 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE 15 MS MAX
 _____ RELEASE 10 MS MAX
 _____ CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO _____
 _____ 2 AMPS @ 28 VDC RESISTIVE _____
 _____ 100,000 OPERATIONS _____

DR. BSH 10/11/01 CK. TLG 10-11-01

CII Technologies
 advanced control electronic solutions

CUST. _____ OPL _____
 CUST. NO. _____ M5752/13-130 _____ REV. _____

3SAT RELAY

3SAT1347A2