

REV. 0

DCO 143070


TOL ± .010 UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C	
RESISTANCE	210 OHMS ±10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	5.4 VDC
MUST RELEASE	3.2 VDC MAX., 0.6 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	
OPERATE 4 MS MAX.	
RELEASE 6 MS MAX.	
CONTACT STABILIZATION 2.0 MS MAX.	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO
	2 AMPS 28 VDC RESISTIVE
	50,000 OPERATIONS

DR. B.D. 6/28/01 CK 6/28/01

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/37-017P REV.

"3SBC" RELAY

3SBC2087A2