

# Power Relay 41063 125°C

- 1 pole 16A, 1 form A (NO) or 1 form B (NC) contact
- Switching capacity 4000VA
- Coil power 360mW
- 4kV/8mm coil-contact, insulation to VDE 0631 and 0700
- Ambient temperature up to 125°C
- Quick connect terminals for load side
- WG version: Materials in accordance to IEC 60335-1

### Typical applications

White goods appliances, oven control, electric heating, power supplies, air conditioning, motors, magnetic valves

## Approvals

VDE REG.-Nr. 3725, UL E214025 Technical data of approved types on request

## **Contact Data**

• ontaot Bata	
Contact arrangement	1 form A (NO) or 1 form B (NC)
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	16A
Limiting making current,	
form A contact, max. 4s, duty factor	10% 25A
Breaking capacity max.	4000VA
Contact material	AgNi, AgCdO
Frequency of operation, with/without loa	ad 600/36000h <sup>-1</sup>

Contact ratings	;		
Туре	Contact	Load	Cycles
IEC61810			
410 63 001	A (NO)	16A, 250VAC resistive, 125°C	50x10 <sup>3</sup>
410 63 001	A (NO)	12A, 250VAC resistive, 125°C	200x10 <sup>3</sup>
410 63 001	A (NO)	16A, 250VAC resistive, 105°C	100x10 <sup>3</sup>
410 63 002	B (NC)	16A, 250VAC resistive, 125°C	50x10 <sup>3</sup>
410 63 005	A (NO)	16A, 250VAC resistive, 125°C	50x10 <sup>3</sup>
410 63 005	A (NO)	12A, 250VAC resistive, 125°C	200x10 <sup>3</sup>
410 63 005	A (NO)	16A, 250VAC resistive, 105°C	100x10 <sup>3</sup>
410 63 006	B (NC)	16A, 250VAC resistive, 125°C	50x10 <sup>3</sup>

Mechanical endurance

>1x10<sup>6</sup> operations





F0248-BA

0.11	Data	
COIL	Data	

Coil voltage range	6 to 60VDC	
Operative range, IEC 61810	1	
Coil insulation system according UL1446	class F	

## Coil versions, DC coil

Coll vers	sions, DC co	11			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
054	6	3.6	0.45	100	360
053	9	5.5	0.68	230	352
050	12	7.3	0.9	400	360
046	24	14.6	1.8	1600	360
043	48	29.2	3.6	6400	360
042	60	36.5	4.5	10000	360

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



## **Insulation Data**

Initial dielectric strength	
between open contacts	1000V <sub>rms</sub>
between contact and coil	4000V <sub>rms</sub>
Clearance/creepage	
between contact and coil	≥8/8mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI250V

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at <a href="http://relays.te.com/definitions">http://relays.te.com/definitions</a>

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change. 1



## Power Relay 41063 125°C (Continued)

#### **Other Data**

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter Resistance to heat and fire WG version according EN60335-1, par.30 Ambient temperature -20 to +125°C Category of environmental protection IEC 61810 RTII - flux proof Terminal type PCB-THT, quick connect for load side Weight 24g Resistance to soldering heat THT IEC 60068-2-20, flux proof version 270°C/10s Packaging/unit tray/75 pcs., box/1050 pcs

## PCB layout / terminal assignment

Bottom view on solder pins



1 form A (NO) contact



1 form B (NC) contact



Typical product code **041063 050 001** 

#### Dimensions



### Product code structure

Туре			
410	<b>)63</b> Power Relay 410 63 125°C		
Coil			
Co	I code: please refer to coil versions table		
Version			
00	1 form A contact (1 NO), AgCdO 002	1 form B contact (1 NC), AgCdO	
00	5 1 form A contact (1 NO), AgNi 006	1 form B contact (1 NC), AgNi	
Version	·		
Bla	<b>nk</b> Standard version		
14/6	Draduat in accordance with IEC COODE 1 (dama	antia analianana)	

Product in accordance with IEC 60335-1 (domestic appliances) WG Other types on request

Product code	Contact arrangement	Contact material	Coil	Version	Part number
0410 63 043 005WG	1 form A (NO) contact	AgNi	48VDC	IEC60335-1 compliant	6-1415536-5
0410 63 046 001		AgCdO	24VDC	Standard	3-1415410-0
0410 63 046 002	1 form B (NC) contact				7-1415534-5
0410 63 050 001	1 form A (NO) contact		12VDC		3-1415410-4
0410 63 050 005WG		AgNi		IEC60335-1 compliant	9-1415535-3
0410 63 053 001		AgCdO	9VDC	Standard	3-1415410-7
0410 63 054 001		-	6VDC		3-1415410-9
0410 63 054 006WG	1 form B (NC) contact	AgNi		IEC60335-1 compliant	7-1415536-6

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request

2

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.