

348461-1 ✓ ACTIVE

AMP | Econoseal


TE Internal #: 348461-1

Silicone, Gray, -40 – 180 °C [-40 – 356 °F] Operating Temperature,
Econoseal

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Primary Product Material: **Silicone**

Primary Product Color: **Gray**

Operating Temperature (Max): 65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 150 °C, 155 °C, 170 °C, 180 °C [149 °F, 158 °F, 167 °F, 176 °F, 185 °F, 194 °F, 212 °F, 221 °F, 230 °F, 248 °F, 257 °F, 266 °F, 284 °F, 302 °F, 311 °F, 338 °F, 356 °F]

Operating Temperature Range: -40 – 180 °C [-40 – 356 °F]

Features

Body Features

Primary Product Material	Silicone
Primary Product Color	Gray

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 150 °C, 155 °C, 170 °C, 180 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][302 °F][311 °F][338 °F][356 °F]
Operating Temperature Range	-40 – 180 °C[-40 – 356 °F]

Packaging Features

Packaging Quantity	5000
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2023
(235)

Candidate List Declared Against: JUN 2020
(209)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Econoseal






Connector Seals & Cavity Plugs(16)



Insertion & Extraction Tools(7)



Other Automotive Connector Accessories(5)



PCB Headers & Receptacles(3)



Primary Wire(1)


Customers Also Bought



TE Part #1-967626-4
Timer Connector Housing



TE Part #928962-2
FF 250 TAB 1.0-2.5MM2 TBR



TE Part #280543
FF 250 REC HSG 2P NYLON NAT



TE Part #1-2232890-9
9P MONOPLUG 2.5 SELECTIVELY LOADED



TE Part #350707-7
UMNL SPLIT PIN 20-14 AUBR L/P



TE Part #DT16-6SB-KP01
PLG, 6P, BLK, E, B



TE Part #1969507-3
250 FASTON HSG., FLAG, REC., 1 POS, BLACK

Documents

Product Drawings

[ECON 3 LC PLUG SILIC](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_348461-1_A.3d_igs.zip](#)

English

[Customer View Model](#)



[ENG_CVM_348461-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_348461-1_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.