



MODEL 4312M3 ACCELEROMETER






DIMENSIONS







6. LOAD RESISTOR(USER INSTALLED) < 250 ohms.

SPECIFICATIONS

- ◆ 4-20mA Signal Output
- MEMS DC Accelerometer
- IP68 Protection
- Low Noise, High Resolution

The Model 4312M3 is 4-20mA output MEMS accelerometer offering both static and dynamic response. The accelerometer is packaged in a corrosion resistant stainless steel housing and is offered in ±2g to ±20g range. The model 4312M3 features an integral cable and is certified to IP68 protection up to 40m depth with an operating temperature range of -40°C to +85°C.

FEATURES

- Stainless Steel Housing
- Corrosion Resistant
- Integral Cable
- ±2g to ±20g Dynamic Range
- DC Response
- Temperature Compensation

APPLICATIONS

- Transportation Measurements
- Structural Monitoring
- Bridge, Tunnel & Dam Monitoring
- Low Frequency Applications
- Submersible Measurements
- Shipboard Installations

WIRE DESIGNATIONS: WHITE = INPUT (EXCITATION)
PINK = OUTPUT
YELLOW = COMMON (CIRCUIT GROUND)
THE OTHER THREE WIRES ARE NOT CONNECTION

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 10Hz and 12Vdc excitation unless otherwise stated. Measurement Specialties reserves the right to update and change these specifications without notice.

| Parameters DYNAMIC | | | | | | Notes |
|--|---|--|--|--|--|---------------------------|
| Model Number Range (g) Sensitivity (mA/g) Frequency Response (Hz) -3dB Cutoff Frequency (Hz' Rolloff Above Cutoff Frequenty (Hz') Non-Linearity & Hysteresis |) 1 ency (dB/dec) - 7 | 4312M3-002 ±2 4.0 0-200 1000 40 700 ±0.5 | 4312M3-005 ±5 1.6 0-300 1000 -40 800 ±0.5 | 4312M3-010 ±10 0.8 0-300 1000 -40 1000 ±0.5 | 4312M3-020 ±20 0.4 0-300 1000 -40 1500 ±0.5 | ±10% ±5% |
| Transverse Sensitivity (%) Damping Ratio Shock Limit (g) Residual Noise (μg RMS) | 0 5 | <3).7 5000 25 | <3 0.7 5000 50 | <3 0.7 5000 100 | <3 0.7 5000 200 | <2 Typical Passband |
| ELECTRICAL Zero Acceleration Output (r Excitation Voltage (Vdc) Quiescent Current (mA) Full Scale Span (mA) Insulation Resistance (MΩ) Load Resistor (Ω) Turn On Time (msec) Grounding | , , , , , , , , , , , , , , , , , , , | 12.0 ±0.25 7 to 24 <15 4 to 20 >100 <250 <100 Case Grounded | , Internally Isola | ted Circuit | | @100Vdc User Installed |
| ENVIRONMENTAL Thermal Zero Shift (%FSO) Thermal Sensitivity Shift (% Operating Temperature (°C) Compensated Temperature Storage Temperature (°C) Humidity | 5/°C) ± 5) - • (°C) C | ±0.04 ±0.04 40 to 85 0 to 65 40 to 85 P68, 40m Dept | h | | | 0 to +65°C 0 to +65°C |
| PHYSICAL Case Material Cable Weight (without cable) Mounting Mounting Torque | 316 Stainless Steel PVC Insulated Leads (6x 0.14 mm²), Braided Shield, PVC Jacket <100 grams 4x #4 or M3 Screws 6 lb-in (0.7 N-m) | | | | | |
| Calibration supplied: | CS-LFREQ-0010 | 0 NIST Trace | NIST Traceable Amplitude Calibration from 1Hz to 100Hz | | | |
| Supplied accessories: | 4x #4-40 (1 ½" length) Socket Head Cap Screw and Washer | | | | | |

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the

Adhesive Mounting Adaptor

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

3-Channel Precision Low Noise DC Amplifier

Optional accessories:

121

AC-A05172

MODEL 4312M3 ACCELEROMETER

ORDERING INFORMATION

PART NUMBERING Model Number+Range+ Cable Length

4312M3-GGG-CCC

I ____Cable Length (-120 is 120 inches) I_____ Range (002 is 2g)

Example: 4312M3-002-120

Model 4312M3, 2g, 120" Cable

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752

Email: customercare.hmpt@te.com

EUROPE

MEAS France SAS a TE Connectivity Company Tel: 800-440-5100

Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015

Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

