



FEATURES

- ±2g to ±200g Dynamic Range
- Amplified Output, Signal Conditioned
- Gas Damped MEMS Sensors
- #26 AWG PFA Jacketed Cable
- Integral Strain Relief
- 4 to 30Vdc Excitation Voltage
- 6000g Shock Protection

APPLICATIONS

- Flight Testing
- Flutter and Nacelle Vibrations
- Road Vehicle Testing
- Structural Testing
- Test and Instrumentation
- Transportation Applications

MODEL 4604 ACCELEROMETER

SPECIFICATIONS

- MEMS DC Accelerometer
- Ultra-Stable, DC to 2000Hz Response
- Exceptional Thermal Performance
- <2.0% Total Error Band
- <0.1% Linearity Accuracy
- Titanium Housing with Rugged Cable

The Model 4604 is a rugged, low-profile MEMS DC accelerometer with exceptional performance over a full operating temperature range of -55° C to $+125^{\circ}$ C. The accelerometers are available in ranges from ±2 to ±200g with a wide bandwidth from DC to 2000Hz. The model 4604 accelerometers incorporate gas damped variable capacitance MEMS sensing element with integral overrange stops for high-g shock protection. The accelerometers are designed for 4 to 30Vdc excitation voltage and incorporate a PFA insulated cable with a rugged strain relief designed for harsh applications.

For a triaxial version, TE Connectivity also offers the model 4630 and 4835A accelerometers.


PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 80Hz and 12Vdc excitation unless otherwise stated. TE Connectivity reserves the right to update and change these specifications without notice.


Parameters DYNAMIC Range (g) Sensitivity, Differential (mV/g) Frequency Response (Hz) Frequency Response (Hz) Non-Linearity (%FSO) Transverse Sensitivity (%) Damping Ratio Shock Limit (g) Residual Noise (µV RMS) Spectral Noise (µg/√Hz)		±2 1000 0-250 0-500 ±0.1 <3 0.7 6000 360 14	±5 400 0-700 0-1000 ±0.1 <3 0.7 6000 380 28	±10 200 0-1000 0-1500 ±0.1 <3 0.7 6000 400 45	±30 67 0-1500 0-2000 ±0.1 <3 0.7 6000 440 137	±50 40 0-1500 0-2000 ±0.1 <3 0.7 6000 480 231	±100 20 0-1500 0-2000 ±0.1 <3 0.7 6000 500 464	±200 10 0-1500 0-2000 ±0.1 <3 0.7 6000 500 920	Notes ±5% ±1dB <1 Typical Passband Passband
ELECTRICAL Zero Acceleration Output (mV) Excitation Voltage (Vdc) Excitation Current (mA) Common Mode Voltage (Vdc) Full Scale Output (differential) Full Scale Output (single-ended) Output Resistance (Ω) Insulation Resistance (MΩ) Turn On Time (msec) Ground Isolation		+0.22 to <100 >100 <100	FSO=2V) 2.22 Vpk (FS	·					Differential @100Vdc
ENVIRONMENTAL Thermal Zero Shift (%FSO/°C) Thermal Sensitivity Shift (%/°C) Operating Temperature (°C) Storage Temperature (°C) Humidity (MEMS Sensor and Electronics) Humidity (Housing) Total Error Band		±0.004 ±0.008 -55 to 125 -55 to 125 Hermetically Sealed Epoxy Sealed, IP65 <2% (RSS of Non-Linearity, Thermal Zero Shift, and Thermal Sensitivity Shift)							
PHYSICAL Case Material Cable Weight (grams) Mounting Mounting Torque		Anodized Aluminum 4x, #26 AWG Conductors, PFA Insulated, Braided Shield, PFA Jacket 10 2x #4 or M3 Screws 6 Ib-in (0.7 N-m)							
Calibration supplied:	CS-FREQ-0	100 NI	ST Traceable Amplitude Calibration from 20Hz to $\pm 5\%$ Frequency Response Limit						
Supplied accessories:	AC-A02285	2x #4-40 (7/16 length) Socket Head Cap Screw and Washer							
Optional accessories:	AC-D02669 AC-D02744 121	Ac	axial Mountir hesive Moun ree Channel	nting Adapto		r			

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. TE Connectivity reserves the right to make changes without further notice to any product herein. TE Connectivity makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does TE Connectivity assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. TE Connectivity does not convey any license under its patent rights nor the rights of others.

DIMENSIONS



SCHEMATIC



ORDERING INFORMATION

4604	GGG	ZZZ	D
Range 002 = 2g 005 = 5g 010 = 10g 030 = 30g 050 = 50g 100 = 100g 200 = 200g			
Cable length			
120 = 120 inches, 10 feet 240 = 240 inches, 20 feet 360 = 360 inches, 30 feet 480 = 480 inches, 40 feet 600 = 600 inches, 50 feet			
197 = 197 inches, 5 meters 394 = 394 inches, 10 meters			
120 = 120 inches, 10 feet 240 = 240 inches, 20 feet 360 = 360 inches, 30 feet 480 = 480 inches, 40 feet 600 = 600 inches, 50 feet 197 = 197 inches, 5 meters			

Example; 4604-010-120-D Model 4604, 10g range, 120inch (10ft) cable length

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752 customercare.hmpt@te.com EUROPE

MEAS France SAS a TE Connectivity Company Tel: +31 73 624 6999 customercare.lcsb@te.com ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 customercare.shzn@te.com

TE.com/sensorsolutions

MEAS France SAS and Measurement Specialties (China) , Inc., are TE Connectivity companies.

TE Connectivity, TE, TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. All Rights Reserved.