





FEATURES

- ±2g to ±200g Dynamic Range
- Amplified Output, Signal Conditioned
- Gas Damped MEMS Sensors
- Hermetically Sealed, Detachable Cable
- Stud Mounting
- 4 to 30Vdc Excitation Voltage
- 6000g Shock Protection

APPLICATIONS

- Flight Testing
- Vehicle Testing
- Structural Testing
- Test and Instrumentation
- Transportation Applications
- Environmental Testing

MODEL 4801A ACCELEROMETER

SPECIFICATIONS

- MEMS DC Accelerometer
- Ultra-Stable, DC to 2000Hz Response
- Hermetically Sealed
- <2.0% Total Error Band
- <0.1% Linearity Accuracy

The Model 4801A is an ultra-stable MEMS accelerometer packaged in a rugged, hermetically sealed stainless steel housing. The accelerometer is available in ranges from ±2 to ±200g with a wide bandwidth from DC to 2000Hz. The model 4801A accelerometers incorporate gas damped variable capacitance MEMS sensing elements that provide exceptional performance over a full operating temperature range of -55°C to +125°C.

The accelerometer is designed for 4 to 30Vdc excitation voltage and is incorporates a #10-32 stud mounting with a detachable model 340A cable assembly

For a triaxial version, TE Connectivity also offers the model 4835A accelerometer.

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 80Hz and 12Vdc excitation unless otherwise stated. TE Connectivity reserves the right to update and change these specifications without notice.

Parameters								
DYNAMIC								Notes
Range (g)	±2	±5	±10	±30	±50	±100	±200	
Sensitivity, Differential (mV/g)	1000	400	200	67	40	20	10	±5%
Frequency Response (Hz)	0-250	0-700	0-1000	0-1500	0-1500	0-1500	0-1500	±5%
Frequency Response (Hz)	0-500	0-1000	0-1500	0-2000	0-2000	0-2000	0-2000	±1dB
Non-Linearity (%FSO)	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	
Transverse Sensitivity (%)	<2	<2	<2	<2	<2	<2	<2	<1 Typical
Damping Ratio	0.7	0.7	0.7	0.7	0.7	0.7	0.7	
Shock Limit (g)	6000	6000	6000	6000	6000	6000	6000	
Residual Noise (µV RMS)	360	380	400	440	480	500	500	Passband
Spectral Noise (μg/√Hz)	14	28	45	137	231	464	920	Passband

ELECTRICAL

Zero Acceleration Output (mV) ±50
Excitation Voltage (Vdc) 4 to 30
Excitation Current (mA) <7

Common Mode Voltage (Vdc) 1.22 Full Scale Output (differential) ±2 Vpk (FSO=2V)

Full Scale Output (single-ended) +0.22 to 2.22 Vpk (FSO=1V)

Output Resistance (Ω) <100 Insulation Resistance ($M\Omega$) >100 Turn On Time (msec) <100

Ground Isolation Isolated from Mounting Surface

ENVIRONMENTAL

Thermal Zero Shift (%FSO/°C) ±0.004 Typical Thermal Sensitivity Shift (%/°C) ±0.008 Typical Operating Temperature (°C) -55 to 125

Operating Temperature (°C) -55 to 125 Storage Temperature (°C) -55 to 125

Humidity Hermetically Sealed, IP67 ¹

Total Error Band <2% (RSS of Non-Linearity, Thermal Zero Shift, and Thermal Sensitivity Shift)

PHYSICAL

Case Material Stainless Steel

Weight (grams) 20

Mounting #10-32 to #10-32 Mounting Stud (included)

Mounting Torque 18 lb-in (2 N-m)

Calibration supplied: CS-FREQ-0100 NIST Traceable Amplitude Calibration from 20Hz to ±5% Frequency Response Limit

Supplied accessories: AC-D02298 10-32 to 10-32 mounting stud

Optional accessories: 340A-XXX Cable Assembly, #28 AWG, -54 to +121°C (XXX designates length in inches, 5ft standard)

121 3-Channel Precision Low Noise DC Amplifier

AC-D02741 Adhesive Mounting Adaptor AC-D04716 Triaxial Mounting Block


The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. TE Connectivity reserves the right to make changes without further notice to any product herein. TE Connectivity makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does TE Connectivity assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. TE Connectivity does not convey any license under its patent rights nor the rights of others.

Differential


@100Vdc

¹ Mating cable needs to also have minimum IP67 rating and be properly sealed to accel connector in accordance with IEC 60529.

DIMENSIONS



SCHEMATIC



ORDERING INFORMATION

4801A	GGGG	D
Range 0002 = 2g 0005 = 5g 0010 = 10g 0030 = 30g 0050 = 50g 0100 = 100g 0200 = 200g		

Example; 4801A-0010-D

Model 4801A, 10g range

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752 customercare.hmpt@te.com

EUROPE

MEAS France SAS a TE Connectivity Company Tel: +31 73 624 6999 customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 customercare.shzn@te.com

TE.com/sensorsolutions

MEAS France SAS and Measurement Specialties (China) , Inc., are TE Connectivity companies.

TE Connectivity, TE, TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. All Rights Reserved.