





MODEL 834M1 ACCELEROMETER

SPECIFICATIONS

- Triaxial Piezoelectric Accelerometer
- ◆ <22µA Current Consumption
 </p>
- Wide Bandwidth to 6kHz
- Circuit Board Mountable

The Model 834M1 is a low cost, board mountable triaxial accelerometer designed for high amplitude embedded shock applications. The accelerometer features a maximum current consumption of 22 micro-amps and incorporates full power and signal conditioning.

The model 834M1 is available in ±2000g to ±6000g ranges and provides a flat frequency response up to greater than 6kHz. The standard model 834 offers the same envelope with a lower maximum current consumption of 4 micro-amps.

FEATURES

- ±2000g to ±6000g Dynamic Range
- Low Cost Triaxial
- Hermetically Sealed
- Piezo-ceramic Crystals
- 40° to +125°C Operating Range
- Single Axis Configurations Available

APPLICATIONS

- Asset Monitoring
- Impact Testing
- System Wake-Up Switch
- Embedded Applications
- Instrumentation

PERFORMANCE SPECIFICATIONS

All values are typical at $+24^{\circ}$ C, 80Hz and 3.3Vdc excitation unless otherwise stated. TE Connectivity reserves the right to update and change these specifications without notice.

Parameters			
DYNAMIC			Notes
Range (g)	±2000	±6000	
Sensitivity (mV/g)	0.62	0.20	±30%
Frequency Response (Hz)	2-6000	2-6000	±2dB
Natural Frequency (Hz)	>30000	>30000	
Non-Linearity (%FSO)	±2	±2	
Transverse Sensitivity (%)	<8	<8	
Shock Limit (g)	10000	10000	
Broadband Noise (μV)	40	30	0.1Hz-10kHz
Spectral Noise (mg/√Hz)	3.2	4.0	@ 10Hz
Spectral Noise (mg/√Hz)	0.6	1.0	@ 100Hz
Spectral Noise (mg/√Hz)	0.2	0.5	@ 1000Hz
ELECTRICAL			
Bias Voltage (Vdc)	Exc Voltage / 2		
Total Supply Current (µA) 1	<22		
Excitation Voltage (Vdc)	3.3 to 5.5		
Output Impedance (Ω)	<100		
Insulation Resistance (MΩ)	>50		@100Vdc
Shielding	100%		

ENVIRONMENTAL

Ground Isolation

Temperature Response (%) -20/+30 from -40°C to +125°C

Operating Temperature (°C) -40 to +125 Storage Temperature (°C) -40 to +125

Humidity Hermetically Solder Sealed

PHYSICAL

Sensing Element Ceramic (shear mode)

Case Material Ceramic Base, Nickel Silver Cover

Weight (grams) 2.6

Calibration supplied: CS-SENS-0100 NIST Traceable Amplitude Calibration at 80Hz

Isolated from Mounting Surface


The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. TE Connectivity reserves the right to make changes without further notice to any product herein. TE Connectivity makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does TE Connectivity assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. TE Connectivity does not convey any license under its patent rights nor the rights of others.

¹ A lower current consumption of 4 micro-amps is available on model 834.

² The model 834M1 is not to be reflow soldered at high temperature, manual soldering is recommended. See operating manual.


³ The model 834M1 can be operated with 2.8V excitation but the full-scale range will be limited. See operating manual for details.

DIMENSIONS



SCHEMATIC

ACCELEROMETER



ORDERING INFORMATION

834M1 **GGGG** Range 2000=2000g 6000=6000g

Example; 834M1-6000 Model 834M1, 6000g range

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752 customercare.hmpt@te.com

EUROPE

MEAS France SAS a TE Connectivity Company Tel: +31 73 624 6999

customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 customercare.shzn@te.com

TE.com/sensorsolutions

MEAS France SAS and Measurement Specialties (China), Inc., are TE Connectivity companies.

TE Connectivity, TE, TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. All Rights Reserved.