

965658-1 ✓ ACTIVE

AMP | Timer Connector System


TE Internal #: 965658-1

Automotive Connector Locks & Position Assurance, Retainer,
Yellow, PA GF, -40 – 120 °C [-40 – 248 °F], Timer Connector System

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Connector & Contact Retention Accessory Type: **Retainer**

Primary Product Color: **Yellow**

Primary Product Material: **PA GF**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	Retainer
--	----------

Body Features

Primary Product Color	Yellow
Primary Product Material	PA GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
------------------	-----

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | Timer Connector System




Automotive Connector Caps & Covers (10)



Automotive Connector Locks & Position Assurance(15)



Automotive Housings(210)



Automotive Terminals(137)



Connector Seals & Cavity Plugs(31)




Crimp Terminal Housings(13)



Insertion & Extraction Tools(18)



Other Automotive Connector Accessories(1)



PCB Headers & Receptacles(77)



Quick Disconnects(4)

Customers Also Bought




TE Part #1-968968-3
2,5MM BU-GEH ASSY2P




TE Part #1718490-1
AMP MCP Unsealed Connector Housings



TE Part #282991-4
20 P.070 NEW GENERATION ASSY C



TE Part #925851-2
140 DIA SOCK.MNL



TE Part #1-2112891-6
36POS,TAB 1.5X0.6,TAB HSG,ASSY




TE Part #5-1803000-7
ANVIL, COMBINATION, END FEED



TE Part #7-2151049-1
OCEAN_2.0_APPLICATOR-S-070F1300



TE Part #967376-1
FLA-STE-GEH KPL16P



Documents

Product Drawings

KONTAKTSICHERUNG

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_965658-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_965658-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_965658-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.